

COVENTRY™ Clean Room Products

Division of Chemtronics

Wrapped Foam Swabs

TDS # 2000

PRODUCT DESCRIPTION

Coventry™ Wrapped Foam Swabs are constructed from reticulated 100 pores per inch medical grade foam which features the best open cell structure, providing excellent particle entrapment characteristics. The foam is thermally bonded to the swab handle without using adhesives.

- Excellent wicking pulls solvent away from surfaces
- Stronger head than other foam swabs
- Fiberless construction does not generate loose fibers or particles
- No adhesives or binders are used in the construction
- Excellent abrasion resistance for scrubbing rough surfaces

TYPICAL APPLICATIONS

Coventry™ Wrapped Foam Swabs can be used to:

- Apply Adhesives or Lubricants into Tight Tolerance Areas
- Splice and Assembly of Fiber Optics
- Dispense or Remove Solvents
- Remove Contamination from Disk Drives
- Scrub Metal Oxides from Electrical Contacts

COMPATIBILITY

Foam Heads are compatible with most common solvents such as isopropyl alcohol and methanol. Compatible with limited exposure to ketones such as acetone or methyl ethyl ketone.

Wood Handles are generally compatible with all solvents except with dilute or weak acids.

Nylon Handles are generally compatible with all common solvents.

AVAILABILITY

- 20050** 2.60" (6.7 cm) Wood Tapered Handle ,
0.12" (3.2mm) Foam Head, 500 swabs/ bag
- 21050** 2.80" (7.1 cm) Nylon Tapered Handle,
0.14" (3.7 mm) Foam Head, 500 swabs/ bag
- 20080** 2.60" (6.7 cm) Wood Tapered Handle ,
0.11" (2.8 mm) Foam Head, 500 swabs/ bag
- 23110** 6.0 " (15.2 cm) Wood, Foam Over Cotton,
0.50" (12.70 mm) Head, 500 swabs/ bag
- 23210** 3.1 " (7.7 cm) Wood, Foam Over Cotton,
0.47" (12.00 mm) Head, 500 swabs/ bag

COVENTRY™ Clean Room Products
Division of Chemtronics.
8125 Cobb Center Drive
Kennesaw, GA 30152 USA
1-770-424-4888 REV. A 08/13)

TECHNICAL HOT LINE 1-800-TECH-401

Wrapped Foam Swab Test Data

| | |
|-------------------------------|-----------------------|
| Head Material | Wrapped Urethane Foam |
| Swab □ | 21050 |
| Head Diameter | 0.03" (0.75 mm) |
| Handle Length | 2.75" (7.0 cm) |
| Particle Counts: | |
| 0.5 - 1 um | 755 |
| 1.0 - 2 um | 97 |
| 2.0 - 5 um | 20 |
| 5.0 - 10 um | 7 |
| 10 - 25 um | 13 |
| over 25 um | 3 |
| TOTAL | 895 |
| NVR (ug/swab) | none detected |
| Chlorides (ug/swab) | 2 |

The swabs were tested by Particle Measurement Technology. All the swabs tests were done using the recommended practices of the Institute of Environmental Science, Swabs and Wipes Working Group.

TECHNICAL AND APPLICATION ASSISTANCE

Coventry™ Clean Room Products provides A technical hotline to answer your technical And application related questions.

The toll free number is: **1-800-TECH-401**

DISTRIBUTED BY:

TECHNICAL HOT LINE 1-800-TECH-401

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [Solder](#) category:

Click to view products by [Chemtronics](#) manufacturer:

Other Similar products are found below :

[91362-6](#) [24-6040-0007](#) [24-7150-8800](#) [24-9574-7619](#) [24-4060-2437](#) [14-6040-0125](#) [04-0595-0000](#) [9SN-310G](#) [5901004](#) [5901006](#) [8001111](#)
[ECC179707EU](#) [SMDLTLFP250T5](#) [41-096-0201N](#) [41-096-0242N](#) [ART.AGT-030](#) [8001263](#) [8001265](#) [389289](#) [54068](#) [0008752](#) [04-6040-0050](#)
[580140](#) [H560103-BULK](#) [H560106-BULK](#) [TDS12AS](#) [5601380](#) [BON-102](#) [BON-102F](#) [BON-102K](#) [BON-102S](#) [BR-102F](#) [560017A](#) [560048](#)
[560051](#) [560069W-LF](#) [5601034](#) [5601053](#) [5601056](#) [5601058](#) [5601157](#) [5601161](#) [5601170](#) [8001092](#) [5601243](#) [0401-08-000179](#) [5601247](#)
[0401-08-000183](#) [5601277](#) [5601376](#) [JD927](#) [JD927-10](#)