
# LABFACILITY

## **TEMPERATURE & PROCESS TECHNOLOGY**

- Precision platinum temperature sensors
- ♦ Pt100, Pt500, Pt1000 and other values available
- Available from stock
- Wire-wound and flat film types Wide range of sizes
- ♦ Tolerance values from Class B to 1/10 Class B
- Single or duplex detectors Specials available to order including alternative R₀ values and nickel resistors



Labfacility offers a wide range of precision platinum temperature sensing resistors in both wire- wound and flat film construction. All standard items are available in quantity from stock; non- standard detectors can be supplied to order.

Platinum wire-wound detectors comprise a pure platinum wire wound into a miniature spiral and located within axial holes in a high purity alumina rod. The freedom of movement of the platinum wire gives good long term stability and a wide operating temperature range of -200 to +800°C. Labfacility wire-wound detectors are cylindrical in shape and ideally suited for housing within a protective metal tube.

Although more expensive than flat film alternatives, wire-wound detectors have a wider temperature range (particularly below -50°C) and are readily available in close tolerance classes.

A range of alternative diameters and lengths is available. Duplex detectors containing two platinum resistors are also available.

Platinum **flat-film detectors** are produced by the deposition of a platinum film on to a flat ceramic substrate, the platinum being sealed to provide protection. Flat-film detectors are available in a range of sizes and are recommended for applications requiring small size, fast response to temperature changes, surface measurement, and resistance to vibration and shock. They are generally less expensive than wire-wound detectors, but the choice of tolerance classes is more limited.

In addition to the standard detectors listed in this data sheet, specials are available including other sizes, duplex detectors, alternative Ro values, and nickel detectors to suit a wide range of applications.

#### LABFACILITY LIMITED

HEADQUARTERS: LABFACILITY LTD, 8 Feltham Business Complex, Browells Lane, Feltham, Middlesex TW13 7LW Tel:+44(0)208818188 Fax +44(0)2088181881 NORTHERN DIVISION:

LABFACILITY LTD, Unit 7 Abbey Way, North Anston Trading Estate, Dinnington, Sheffield 531 7]L,UK. Tel:+44(0)1909 569446 Fax:+44(0)1909 550632 SOUTHERN and EXPORT DIVISION:

LABFACILITY LTD, Unit 7 Southern Cross Industrial Estate Shripney Road, Bognor Regis, West Sussex PO22 9SD Tel: +44(0)1243 871280 Fax +44(0)1243 871281;





#### **SPECIFICATIONS**

Sensor type

Unless stated all detectors are Pt100 to BS EN60751:1996, BS1904:1984, DIN 43760:1980and IEC 751:1983

100 Ohms

Temperature range

Wire wound: -200 to +800°C

Flat film:

-50°C to maximum value shown below.

#### Resistance v temperature and tolerances for Pt100 thermometers to IEC 751

| Tempera | ture Resistance |                | Tolerance | 444            | 4.5  | Tempera | ture Resistance | 表面             | Tolerance | 并准备            |           |
|---------|-----------------|----------------|-----------|----------------|------|---------|-----------------|----------------|-----------|----------------|-----------|
| (°C)    | (Ω)             | Class<br>(±°C) |           | Class<br>(±°C) |      | (°C)    | (Ω)             | Class<br>(±°C) | A<br>(±Ω) | Class<br>(±°C) | B<br>(±Ω) |
| -200    | 18.52           | 0.55           | 0.24      | 1.3            | 0.56 | 500     | 280.98          | 1.15           | 0.38      | 2.8            | 0.93      |
| -100    | 60.26           | 0.35           | 0.14      | 0.8            | 0.32 | 600     | 313.71          | 1.35           | 0.43      | 3.3            | 1.06      |
| 0       | 100.00          | 0.15           | 0.06      | 0.3            | 0.12 | 650     | 329.74          | 1.45           | 0.46      | 3.6            | 1.13      |
| 100     | 138.51          | 0.35           | 0.13      | 0.8            | 0.30 | 700     | 345.28          | # <u># #</u>   | 114       | 3.8            | 1.17      |
| 200     | 175.86          | 0.55           | 0.20      | 1.3            | 0.48 | 800     | 375.70          | <u> </u>       | Maid at 8 | 4.3            | 1.28      |
| 300     | 212.05          | 0.75           | 0.27      | 1.8            | 0.64 | 850     | 390.48          | 1              |           | 4.6            | 1.34      |
| 400     | 247.09          | 0.95           | 0.33      | 2.3            | 0.79 | 3.444   | ·图集計畫 使         | # W            | 4447      |                | \$ # J    |

**Tolerances** 

Class B Class A  $\pm (0.3^{\circ}\text{C} + 0.005\text{t})$ 

Where t is the measured temperature

 $\pm (0.15^{\circ}C + 0.002t)$ 

1/3 Class B

 $\pm (0.1^{\circ}\text{C at }0^{\circ}\text{C})$ 

1/5 Class B

±(0.06°C at 0°C)  $\pm (0.03^{\circ}\text{C at }0^{\circ}\text{C})$ 

1/10 Class B

Note: 1/3, 1/5 and 1/10 Class B

Tolerances apply at 0°C


Specifications may be subject to change

#### **Order Codes and Dimensions**

| Oraci Godes and Differsions |                 |                |            |  |  |  |  |  |
|-----------------------------|-----------------|----------------|------------|--|--|--|--|--|
| Wire Wound Detectors, PT100 |                 |                |            |  |  |  |  |  |
| Dimensions                  | Tolerance Class |                | Order Code |  |  |  |  |  |
| Dia x length mm)            |                 | No.            | 逐起等表层      |  |  |  |  |  |
| 2.8 x 25                    | В               | P100/2528 B    | DA-016     |  |  |  |  |  |
| 2.8 x 25                    | Α               | P100/2528 A    | DA-017     |  |  |  |  |  |
| 2.8 x 25                    | 1/3             | P100/2528 1/3  | DA-018     |  |  |  |  |  |
| 2.8 x 25                    | 1/5             | P100/2528 1/5  | DA-019     |  |  |  |  |  |
| 2.8 x 25                    | 1/10            | P100/2528 1/10 | DA-020     |  |  |  |  |  |
| 1.5 x 25                    | В               | P100/2515 B    | DA-026     |  |  |  |  |  |
| 2.8 x 15                    | В               | P100/1528 B    | DA-041     |  |  |  |  |  |
| 2.8 x 15                    | Α               | P100/1528 A    | DA-042     |  |  |  |  |  |
| 2.8 x 15                    | 1/3             | P100/1528 1/3  | DA-043     |  |  |  |  |  |
| 2.8 x 15                    | 1/5             | P100/1528 1/5  | DA-044     |  |  |  |  |  |
| 2.8 x 15                    | 1/10            | P100/1528 1/10 | DA-045     |  |  |  |  |  |
| 2.4 x 15                    | В               | P100/1524 B    | DA-046     |  |  |  |  |  |
| 1.6 x 15                    | В               | P100/1516 B    | DA-056     |  |  |  |  |  |
| 1.5 x 15                    | В               | P100/1515 B    | DA-061     |  |  |  |  |  |
| 1.5 x 15                    | Α               | P100/1515 A    | DA-062     |  |  |  |  |  |
| 1.5 x 15                    | 1/3             | P100/1515 1/3  | DA-063     |  |  |  |  |  |
| 1.5 x 15                    | 1/5             | P100/1515 1/5  | DA-064     |  |  |  |  |  |
| 1.5 x 15                    | 1/10            | P100/1515 1/10 | DA-065     |  |  |  |  |  |
| 0.8 x 15                    | В               | P100/0815 B    | DA-081     |  |  |  |  |  |
| 0.8 x 15                    | Α               | P100/0815 A    | DA-082     |  |  |  |  |  |
| 0.8 x 15                    | 1/3             | P100/0815 1/3  | DA-083     |  |  |  |  |  |
| 0.8 x 15                    | 1/5             | P100/0815 1/5  | DA-084     |  |  |  |  |  |
| 0.8 x 15                    | 1/10            | P100/0815 1/10 | DA-085     |  |  |  |  |  |

**Dimensions** 

Individual dimensions are given in Order Codes & Dimensions below.



| _ | Flat-film detectors, Pt100 and Pt1000 |                                      |       |                  |        |  |  |  |  |
|---|---------------------------------------|--------------------------------------|-------|------------------|--------|--|--|--|--|
| • | Sensor type                           | Sensor type Dimensions Tolerance Max |       |                  |        |  |  |  |  |
|   |                                       | WxLxH<br>(mm)                        | Class | temperature (°C) | Code   |  |  |  |  |
|   | Pt100Ω                                | 2 x 5 x 1.1                          | В     | 500              | DM-503 |  |  |  |  |
|   | Pt100Ω                                | 2 x 5 x 1.1                          | Α     | 400              | DM-508 |  |  |  |  |
|   | Pt100Ω                                | 1.7 x 5 x 1.1                        | В     | 600              | DM-385 |  |  |  |  |
|   | Pt100Ω                                | 2 x 10 x 1.4                         | В     | 600              | DM-333 |  |  |  |  |
|   | Pt100Ω                                | 2 x 10 x 1.4                         | Α     | 400              | DM-334 |  |  |  |  |
|   | Pt1000Ω                               | 2 x 10 x 1.1                         | В     | 500              | DM-507 |  |  |  |  |
|   | Pt1000Ω                               | 2 x 10 x 1.4                         | В     | 600              | DM-367 |  |  |  |  |

Class A and B detectors are readily available from stock.

When ordering alternative tolerance devices please call to first to confirm availability.

For sizes and types not listed, contact sales office

Labfacility manufactures and stocks a wide range of RTD probes





#### LABFACILITY LIMITED

HEADOUARTERS:

LABFACILITY LTD, 8 Feltham Business Complex, Browells Lane, Feltham, Middlesex TW13 7LW Tel:+44(0)208818188 Fax +44(0)2088181881 NORTHERN DIVISION:

LABFACILITY LTD, Unit 7 Abbey Way, North Anston Trading Estate, Dinnington, Sheffield 531 7]L,UK. Tel:+44(0)1909 569446 Fax:+44(0)1909 550632 SOUTHERN and EXPORT DIVISION:

LABFACILITY LTD, Unit 7 Southern Cross Industrial Estate Shripney Road, Bognor Regis, West Sussex PO22 9SD

Tel: +44(0)1243 871280 Fax +44(0)1243 871281;

### **X-ON Electronics**

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Other Tools category:

Click to view products by Labfacility manufacturer:

Other Similar products are found below:

CR-05FL7--150R CR-05FL7--698K 899-2-KT46 899-5-KT46 CR-0AFL4--332K CR-12FP4--260R CRCW04021100FRT7

CRCW04021961FRT7 5800-0090 CRCW04024021FRT7 CRCW040254R9FRT7 CRCW0603102JRT5 59065-5 00-8273-RDPP 00-8729-WHPP 593033 593058 593072 593564100 593575 593591 593593 011349-000 LTILA506SBLAMNBL CRCW08052740FRT1 LUC-012S070DSM LUC-018S070DSP 599-2021-3-NME 599-JJ-2021-03 00-5080-YWPP 5E4750/01-20R0-T/R LW1A-L1-GL LW1A-P1-GD LW1L-A1C10V-GL LW1L-M1C70-A 0202-0173 00-9089-RDPP 00-9300-RDPP CRCW2010331JR02 01-1003W-8/32-10 601-GP-08-KT39 601-JJ-06 601-SPB 601YSY 602-JJ-03 602SPB 602Z 603-JJ-07-FP 603-JJY-04 604J