

SD200-12-22-041

Silicon Photodiode

The SD 445-14-21-305 is a 5.1mm diameter (20mm²) active area BLUE enhanced silicon PIN photodiode, packaged in a hermetically sealed TO-8 metal package.

Applications

Instrumentation
Medical
Industrial
Analytical Equipment

Features

Low Noise	
Blue Enhanced	
High Shunt Resistance	
High Reponsivity	








Absolute Maximum Ratings at T_A=23 °C

Parameter	Symbol	Min	Max	Unit
Reverse Voltage	V _R	-	75	V
Operating Temperature	T _{op}	-40	+125	°C
Storage Temperature	T _{stg}	-55	+150	°C

Typical Electro-Optical Specifications at $T_A = 23 \text{ °C}$


Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
Active Area	-	AA	-	20	-	mm²
Dark Current	V _R =5V	I _D	-	6.5	26.0	nA
Shunt Resistance	V _R =10mV	R _{sh}	70	-	-	MΩ
Junction Capacitance	V _R =0V; f=1MHz	C」	-	-	415	pF
	V _R =10V; f=1MHz	C」	-	75	125	pF
Spectral Application Range	Spot Scan	λ	350	-	1100	nm
Responsivity	λ =450nm, V _R =0V	R	0.20	0.28	-	A/W
Breakdown Voltage	I=10μA	$V_{\rm BD}$	-	50	-	V
Noise Equivalent Power	V _R =5V@λ=Peak	NEP	-	1.6x10 ⁻¹³	-	W/ √ Hz
Response Time (10% to 90%)	RL=50 Ω , V _R =0V, λ =660nm	T _R	-	125	-	nS
	RL=50Ω, V _R =5V, λ=660nm	T _R	-	16	-	nS

Spectral Response



Mechanical Specifications

Units are in inches [mm]







Care and handling instructions

Your optoelectronic components are packaged and shipped in opaque, padded containers to avoid ambient light exposure and damage due to shock from dropping or jarring.

Care must be taken to avoid exposure to high ambient light levels, particularly from tungsten sources or sunlight.

- These components can be rendered inoperable if dropped or sharply jarred. The wire bonds are delicate and can become separated from the bonding pads when the component is dropped or otherwise receives a sharp physical blow.
- Most windows on photodiodes are either silicon or quartz. They should be cleaned with isopropyl alcohol and a soft (optical grade) pad.
- Photodiode exposure to extreme high or low storage temperatures can affect the subsequent performance. Maintain a non-condensing environment for optimum performance and lifetime.
- All devices are considered ESD sensitive. The photodiodes are shipped in ESD protective packaging. When unpacking and using these products, anti-ESD precautions should be observed.
- Photodiode packages and/or operation may be impaired if exposed to CHLOROETHENE, THINNER, ACETONE, TRICHLOROETHYLENE or any harsh chemicals.

Legal Disclaimer

Information in this data sheet is believed to be correct and reliable. However, no responsibility is assumed for possible inaccuracies or omission. Specifications are subject to change without notice.



Most of our standard catalog products are RoHS Compliant. Please contact us for details.

- Optoelectronic components in plastic packages should be given special care. Clear plastic packages are more sensitive to environmental stress than those of black plastic. Storing devices in high humidity can present problems when soldering. Since the rapid heating during soldering stresses the wire bonds and can cause wire to bonding pad separation, it is recommended that devices in plastic packages to be baked for 24 hours at 85°C.
- The leads on the photodiode SHOULD NOT BE FORMED. If your application requires lead spacing modification, please contact Advanced Photonix Applications group at Techsupport@advancedphotonix.com before forming a product's leads. Product warranties could be voided.
- Most devices are provided with wire or pin leads for installation in circuit boards or sockets. Observe the soldering temperatures and conditions specified below:
 - Soldering Iron: Soldering 30 W or less
 - Temperature at tip of iron 300°C or lower.
 - Dip Soldering: Bath Temperature: 260±5°C.
 - Immersion Time: within 5 Sec.
 - Soldering Time: within 3 Sec.
 - Vapor Phase Soldering, Reflow Soldering: DO NOT USE



www.advancedphotonix.com / +1 805 987 0146

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Photodiodes category:

Click to view products by Advanced Photonix manufacturer:

Other Similar products are found below :

 BPW 34 FAS-Z
 67-21SYGC-S349-TR8
 HFD3081-108-XBA
 BPW 34 S E9601
 MICROFJ-60035-TSV-TR
 ZSPD-Z3215B-10-Z2
 PT908

 7B(BIN4)
 PT204-6B(BY)(K)
 PT928-6C/MA(XBY)
 PT908-7C(BIN5)
 PT968-8B(6-2)
 PT968-8C(6-1)
 PT204-6B(BY)(J)
 PT968-8B(6-1)

 PD70-01C/TR7(BY)
 PT968-8C(6-2)
 XYC-PD3020F90-S3
 ZSPD-Z3215C-10A-Z2
 ZSPD-Z3227B-10C-Z3
 ZSPD-Z3227C-10-Z3
 PD15

 22C/TR8(BY)
 ZPD-Z3224B-T26-T15(YPX)
 ZSPD-Z5042C-A10-Z1
 ZSPD053B-S40
 PT334-6C(BY)(K)
 PT968-8C(X1-X4)XBY
 PT334

 6B(BY)(K)
 PT928-6C(5-2)
 PT334-6B(BY)(L)
 PT333-3B(BY)(K)
 PT334-6B(BY)(M)
 XYC-PD204B-L1
 XYC

 PD3A940FC-F1
 XYC-PD4335F90-E2
 ZSPD808B
 ZSPD818B
 ZSPD034B-N
 ZSPD888C
 ZSPD053B-90-S90
 PD234-6B/L3
 PD70

 01C/TR7(ORI)
 NCD2516RGI1
 NCD3220S1
 NCD4437S1
 NCD1816RGI1
 XYC-PD333B-L2
 XYC-PD5AB940DC-E9
 XL-504PDC
 XL-504PDC