



PRODUCT

Integrity 100% polyester 140gsm wipes

600-0220

The heavy weight laser sealed edged Polyester wiper is a double knit 100% continuous-filament polyester. All four edges are laser cut and sealed to prevent particle and fibre release.

FEATURES

- Laser sealed edge ensures ultra low lint and particle level
- Good absorbency and wiping efficiency
- · Resists abrasion under rigorous use
- Solvent safe, double bagged and vacuum cleanroom packed
- Available sterile by gamma irradiation



APPLICATIONS

- Suitable for class ISO4 ISO6 cleanrooms
- Cleaning of surfaces to control submicron particles, fibres, and chemical residue

| PRODUCT CODE | SIZE (in) | STERILITY | QUANTITY (per pack) |
|--------------|-----------|-------------|------------------------|
| 600-0220 | 9 x 9 | Non-sterile | 100 (flat pack) |
| 600-0221 | 9 x 9 | Sterile | 10 (flat pack) |

To request a quotation or for more information, please call **+44 (0)1473 836205** email **info@integritycleanroom.com** or visit **www.integritycleanroom.co.uk**

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.





PERFORMANCE CHARACTERISTICS

| Basis weight | 140 gsm | | | |
|--------------------------------|----------|--|--|--|
| Thickness (micrometer) | 0.48mm | | | |
| Absorbency (IEST-RP-CC 004.3) | | | | |
| Sorptive capacity | 320ml/m2 | | | |
| Rate (Drop Disappearance mtd.) | 0.5 sec | | | |

| ION CONTENT (IEST-RP-CC 004.3, THOROUGH EXTRACTION METHOD) | | | |
|--|---------------|--|--|
| Chloride (CI) | 0.000174 mg/g | | |
| Nitrates (NO3) | 0.000019 mg/g | | |
| Nitrite (NO2) | 0.000025 mg/g | | |
| Sulphate (SO4) | 0.000083 mg/g | | |
| Sodium (Na) | 0.000312 mg/g | | |
| Potassium (K) | 0.000227 mg/g | | |
| Magnesium (Mg) | 0.000049 mg/g | | |
| Calcium (Ca) | 0.000021 mg/g | | |

| NONVOLATILE RESIDUE, NVR (IEST-RP-CC 004.3,ANALYSIS FOR UNSPECIFIED EXTRACTABLE MATTER) | | | | |
|---|--|--|--|--|
| IPA Extractant | 0.52 mg/g | | | |
| DIW Extractant | 0.14 mg/g | | | |
| FTIR | NO Silicon Oil, Amide and DOP detected | | | |

| RELEASABLE PARTICLES | | | |
|---|--|--|--|
| LPC (> 0.5 um) | 6.5 x 10 ⁶ particles/m ² | | |
| (IEST-RP-CC 004.3-orbital shake mtd) | | | |
| APC (Helmke Drum Test @10rpm); > 0.5 um | 50 counts/pc./cfm -9"x9" | | |
| (IES-RP-CC003.2) | 9.71 x 10.2 counts/m2/cfm | | |

To request a quotation or for more information, please call **+44 (0)1473 836205** email **info@integritycleanroom.com** or visit **www.integritycleanroom.co.uk**

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Chemicals category:

Click to view products by Antistat manufacturer:

Other Similar products are found below:

DP-605NS 3125-9S 3748-Q-58"x8" S1009-KIT-A-CS8606 DP100-200ML 152-KA-NC 3789-Q 9729 9223 3748PG 9945 7000000275

1601 842AR-15ML 841AR-150ML 842AR-P 843WB-15ML 8462-85ML 4352-1L 4354-1L 838AR-P 838AR-15ML 419D-P-BK 419D-P-GR 419D-P-WH 8MT-450 8MT-25 832HD-25ML 8616-25ML 832FX-450ML 834ATH-375ML 832HD-400ML 843AR-340G 843ER-800ML 847-1P 4228-225ML 419D-55ML 8800-375ML 8810-375ML 8820-2.55L 419E-340G 842UR-12ML 419D-1L 10447 4140A-945ML FW2170 561, 19G 5922, 60ML 510, 50ML 5188, 50ML