

PRODUCT

PRINCIPLE

Nitrile Gloves

DESCRIPTION

Integrity Cleanroom PRINCIPLE Nitrile Gloves are ambidextrous, with a beaded cuff which has been designed for extra protection. The textured surface and enhanced grip makes these nitrile gloves ideal for handling delicate items.

Our gloves are powder and latex free, assisting in reducing the risk of an allergic reaction.


FEATURES

- Class 100
- 100% Nitrile Butadiene Rubber
- Length: 300mm / 12 inch
- Powder free and latex free
- Beaded cuff with textured fingers
- White
- 5 year shelf life from manufacture

PRODUCT CODE	DESCRIPTION	SIZE	LENGTH (INCH)	QUANTITY
602-0410	PRINCIPLE Non-Sterile Nitrile Glove	S	12	100 pcs/pack
602-0411	PRINCIPLE Non-Sterile Nitrile Glove	M	12	100 pcs/pack
602-0412	PRINCIPLE Non-Sterile Nitrile Glove	L	12	100 pcs/pack
602-0413	PRINCIPLE Non-Sterile Nitrile Glove	XL	12	100 pcs/pack

To request a quotation or for more information, please call **+44 (0)1473 836205**
 email info@integritycleanroom.com or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.

PROPERTIES	RESULT
Surface	Finger textured
Colour	White
Length	300mm / 12 inch
Thickness	5.0 mil (±1)
Tensile strength	Min 15 Mpa
Elongation	600%
Packing style	100 pcs per bag 10 bags per carton (1000 pcs in total)
Physical Properties	Meets the requirements of the Glove Standard EN420:2003+A1:2009 and the European Medical Gloves Standard EN455 (Parts 1, 2, 3, 4) & EN374:-2016 (Part 1, 2, 3, 4 and 5). Product fulfills the cleanroom specifications of nitrile gloves as per ISO 23464:2020.
Material	100% Nitrile Butadiene Rubber
Shelf life	Five (5) years from date of manufacture
Storage instructions	Store in a cool dry place (< 40°C) away from direct light sources
Batch Traceability	The traceability numbers are shown on the sealed inner PE bag and the carton
Liquid Particle Counts (as determined by IES-RP-C005.4)	< 1200 particle counts cumulative at 0.5micron
Organics (IES-RP-CC005.4)	Silicone Oil Free, detected by FTIR Spectroscopy
Non-Volatile Residue	<10 microgram/ sq. cm
ESD Parameters (ASTM D-257)	Surface Resistance - ≤10E10 Ohms/sq. Decay Time (Sec) - ≤0.5 Tribo Charge (Volts) - ≤20
Dimension Criteria	Length: 300 ± 10 mm Palm Width: 80-89 to 110-116 mm Single Wall thickness: Finger thickness: 0.13 ± 0.03 mm Palm thickness: 0.10 ± 0.02 mm Cuff thickness: 0.06 ± 0.02 mm

Ionic Burden (microgram/ sq cm) (as determined by IES-RP-C005.4)

Fluoride	<0.030	Sulphate	<0.800
Chloride	<1.200	Nitrate	<1.000
Phosphate	<0.800	Bromide	<0.050
Sodium	<0.050	Magnesium	<0.004
		Potassium	<0.050

To request a quotation or for more information, please call **+44 (0)1473 836205**
 email info@integritycleanroom.com or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [Antistat](#) manufacturer:

Other Similar products are found below :

[001-0001](#) [001-0003](#) [001-0006](#) [001-0008](#) [001-0009](#) [001-0014](#) [001-0017](#) [001-0021](#) [001-0023](#) [001-0028](#) [001-0029](#) [001-0035](#) [003-0001](#) [003-0002](#) [003-0003](#) [003-0011](#) [003-0012](#) [010-0001](#) [010-0005](#) [010-0006](#) [010-0008](#) [010-0011](#) [010-0012](#) [010-0013](#) [010-0014](#) [010-0015](#) [010-0024](#) [010-0025](#) [010-0028](#) [010-0029](#) [010-0035](#) [010-0041](#) [010-0042](#) [010-0047](#) [010-0055](#) [010-0058](#) [010-0060](#) [010-0085](#) [010-0112](#) [010-0115](#) [013-0001](#) [013-0003](#) [013-0004](#) [013-0005](#) [013-0006](#) [013-0010](#) [018-0007](#) [018-4407](#) [019-0003](#) [025-0004](#)