


Bubblemat Connect Anti Fatigue Mat

Interlocking tiles with high anti-fatigue properties



- Durable anti-fatigue matting system.
- Raised bubbled surface to stimulate blood circulation and reduction of fatigue.
- Interlocking system provides flexibility in the type of shape that can be created.
- Soft but sturdy rubber material offers protection from adverse effects from cold, hard concrete floors.
- Rubber is naturally slip resistant.



Parts

Part Number	Size	Colour	Weight
BF010007	50 cm x 50 cm (Middle)	Black	2.05 kg
BF010008	50 cm x 50 cm (End)	Black	2.05 kg
BF010009	50 cm x 50 cm (Corner)	Black	2.05 kg
BF010708	50 cm x 50 cm (End)	Black/Yellow	2.05 kg
BF010709	50 cm x 50 cm (Corner)	Black/Yellow	2.05 kg

Technical Specification

Material	Natural rubber
Surface Finish	Bubble
Product Height	13.5 mm
Product Weight	5.75kg
Operating Temperature	-30°C to +50°C
Resistance to Chemicals	Not resistant to fat and mineral oil
Environmental Resistance	Suitable for dry indoor environments
UV Resistance	Yes
Installation Method	Loose lay interlocking mats
Cleaning Method	Use a high pressure hose (not exceeding 60psi) to remove the dirt and debris on the mats. For best

results use a mild detergent (pH 4.0-9.0) to clean the mats. Do not use steam or degreasers or caustic chemicals. Do not mechanically scrub the mats.

Country of Origin	Sri Lanka
Tensile Strength	3 MPa
250%	Manufacturing process
Compression moulding	

Get in touch | To order FREE samples or arrange a site visit please call +44 (0)116 240 1088 or email sales@cobaeurope.com

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [PPE Safety Equipment / Lockout Tagout](#) category:

Click to view products by [COBA](#) manufacturer:

Other Similar products are found below :

[AB12-SF1260](#) [GPSL-6KA](#) [GPSL-8MKEY](#) [35035](#) [702201756](#) [PSL-PC38-33](#) [7100078986](#) [132231](#) [44-809](#) [G3000NUV-VI-R](#) [STC1165](#)
[STC5951](#) [DAF010701](#) [WC000003](#) [509-0015](#) [509-0017](#) [509-0019](#) [509-0020](#) [509-0021](#) [509-0022](#) [509-0002](#) [509-0003](#) [509-0004](#) [509-0006](#)
[109-0920](#) [109-0917](#) [109-0918](#) [109-0919](#) [DYC200-01-01-9-DYCLEAN-S](#) [109-0027](#) [X2A](#) [26702](#) [28774](#) [SFTY PADLOCK NYLON 38MM](#)
[SHA YELLOW 6/PAC](#) [FMB12](#) [FMB14](#) [FMB14 MIDI](#) [FMB18](#) [FMB38](#) [FMFR 12](#) [FMFR 12-AUT](#) [FMFR 14](#) [FMFR 14 MIDI](#) [FMFR 18](#)
[FMFR 38](#) [FML 12](#) [FML 14](#) [FML 14 MIDI](#) [FML 18](#) [FMR 12](#)