



## Entra-Clean Hygiene+

The washable doormat that actively kills germs



- Removes visible dirt and kills invisible microbes.
- HygienePlus means the mat is treated with the EU-registered biocide, BI-OME registered with OEKO-TEX® an antimicrobial and virus reducing technology. BI-OME works by effectively killing bacteria when contact is made with the mat.
- Although the treatment is a highly effective antimicrobial agent, it does not cause any skin irritations.
- A new concept in entrance matting.
- Improve floor level hygiene around your business – important whilst fighting Covid-19 and beyond.
- More sustainable – less frequent washing required, and on lower temperatures. Free of metals.
- Fully machine washable – with no reduction in active cleaning power for the life of the mat.
- Suitable for all facilities, in particular offices, hotels and leisure, retirement homes and healthcare settings.
- Reduces annoying odours caused by bacteria and fungi.

### Styles Available



Anthracite



Grey



Brown

### Parts

Part Number	Size	Colour	Weight
EC010001	0.6m x 0.9m	Anthracite	1.5Kg
EC010002	0.8m x 1.2m	Anthracite	2.7Kg
EC010003	0.9m x 1.5m	Anthracite	3.8Kg
EC010004	1.2m x 1.8m	Anthracite	6.1Kg
EC010005	1.2m x 2.4m	Anthracite	8.1Kg
EC060001	0.6m x 0.9m	Grey	1.5Kg
EC060002	0.8m x 1.2m	Grey	2.7Kg
EC060003	0.9m x 1.5m	Grey	3.8Kg
EC060004	1.2m x 1.8m	Grey	6.1Kg
EC060005	1.2m x 2.4m	Grey	8.1Kg

### Technical Specification

<b>Material</b>	100% Polyamide
<b>Surface Finish</b>	Superior non-slip vinyl backing
<b>Product Height</b>	9mm
<b>Typical Applications</b>	Interior entrances as a loose-lay mat.
<b>Installation Method</b>	Loose lay
<b>Cleaning Method</b>	Vacuum clean regularly. Machine washable (30°C)
<b>Country of Origin</b>	Belgium
<b>Registered with:</b>	OEKO-Tex®

EC050001	0.6m x 0.9m	Brown	1.5Kg
EC050002	0.8m x 1.2m	Brown	2.7Kg
EC050003	0.9m x 1.5m	Brown	3.8Kg
EC050004	1.2m x 1.8m	Brown	6.1Kg
EC050005	1.2m x 2.4m	Brown	8.1Kg

**Treatment:** BI-OME (Biocide registered with ECHA (PT2, PT7, PT9)).

**Treatment lifespan** Treatment with BI-OME stays active for the lifetime of the mat.

Get in touch | To order FREE samples or arrange a site visit please call +44 (0)116 240 1088 or email [sales@cobaeurope.com](mailto:sales@cobaeurope.com)

## X-ON Electronics

Largest Supplier of Electrical and Electronic Components

*Click to view similar products for [PPE Safety Equipment / Lockout Tagout](#) category:*

*Click to view products by [COBA](#) manufacturer:*

Other Similar products are found below :

[AB12-SF1260](#) [GPSL-6KA](#) [GPSL-8MKEY](#) [35035](#) [702201756](#) [PSL-PC38-33](#) [7100078986](#) [132231](#) [44-809](#) [G3000NUV-VI-R](#) [STC1165](#)  
[STC5951](#) [WC000003](#) [509-0015](#) [509-0017](#) [509-0019](#) [509-0020](#) [509-0021](#) [509-0022](#) [509-0002](#) [509-0003](#) [509-0004](#) [509-0006](#) [109-0920](#)  
[109-0917](#) [109-0918](#) [109-0919](#) [DYC200-01-01-9-DYCLEAN-S](#) [109-0027](#) [X2A](#) [26702](#) [28774](#) [SFTY PADLOCK NYLON 38MM SHA](#)  
[YELLOW 6/PAC](#) [FMFR 12](#) [FMFR 12-AUT](#) [FMFR 14](#) [FMFR 14 MIDI](#) [FMFR 18](#) [FMFR 38](#) [FML 12](#) [FML 14](#) [FML 14 MIDI](#) [FML 18](#)  
[FMR 12](#) [FMR 18](#) [FMR 38](#) [603](#) [30-551-3040](#) [30-552-0010](#) [30-552-6012](#)