

AMT ENCODER SERIES

Assembly Instructions







Sleeve Sizes:

- 2 mm= Light Blue 3 mm= Orange
- 3.175 mm (1/8")= Purple
- 4 mm= Gray
- 4.76 mm (3/16")= Yellow
- 5 mm= Green
- 6 mm= Red
- 6.35 mm (1/4")= **White**
- 8 mm = Blue











STEP 1




- 1. Insert Tool A as a spacer that defines the distance to the mounting surface.
- 2. Slide appropriate sized Sleeve over shaft all the way down to Tool A.
- 3. Slide Shaft Adaptor over Sleeve.
- 4. Use Tool C to press Shaft Adaptor over Sleeve (ensure Shaft Adapter and Tool C spline alignment) until flush with Tool A.

STEP 2




- 1. Remove Tools A and C.
- 2. Place Base on motor, with Tool C used as a centering tool.


STEP 3




- 1. Align Tool C with flange on Base.
- 2. Slide Base and Tool C onto motor, centering onto the Shaft Adapter.



- Fasten the Base on the motor (Tool C may need to be rotated to allow for some mounting configurations).
- 2. Remove Tool C.



- Snap the Top Cover onto the Base, carefully observing that the teeth of the Shaft Adaptor align with the grooves in the hub.*
- * We recommend no more than three cycles of mounting and removal of the AMT top cover base. Multiple cycles of mounting and removing the top cover can cause base fatigue over time and affect encoder performance.



- 1. Make sure the snaps are fully engaged by pressing on the Hub with the reverse side of Tool C.
- 2. When assembly is finished, the Shaft Adaptor, Sleeve and Rotor Hub should all be flush with the Motor Shaft rotating freely.

For additional instructions or information contact customer support at: 877.323.3576

For more information visit: www.cuidevices.com/amt

CUI DEVICES

6405 SW Rosewood St, Ste C Lake Oswego, OR 97035

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Encoders category:

Click to view products by CUI Devices manufacturer:

Other Similar products are found below:

6-1393048-0 6-1393048-5 62AG22-H5-P 62B22-LP-030C 63K25 63K32 63KS100 63KS64 63R100 63R50-020 63RS256-060 700-09-36
RE12D300-201-1 1393047-3 2-1393047-2 T101-5C2-111-M1 T101-5C3-111-M1 T101-5C4-111-M1 385001M0439 385001M0216
V23401H1409B101 V23401T8002B802 V23401U6019B609 E69-1 E69DF10 E69-FCA 62B11-LP-100S 62B11-LPP-040C 62N11-P
62S22-H9-120S 62S30-L0-200C 62V15-02-080S 63K64 63KS100-040 63R64-050 63RS64 700-16-16 V23401D3002B301 3-1393048-1
63KS128 63KS256 1-1879391-5 GH65C11-N-SO 62S15-M0-P 1393047-1 E69-FCA02 E69-FCA04 E69-DF20 E69-DF2 63R50