


TECHNICAL DETAIL & LAB TEST REPORT

FEATURES AND PATTERN

www.dbmlighting.com

CR-102+ Cree MK-R

Lens part number	CR102		
Tested with LED	Cree MK-R		
Lens Material	PMMA		
FWMH ^o	26		




OPTICAL EFFICIENCY

Half Angle Divergence: 13.0 deg

HAD Efficiency: 39 %

Collection Efficiency: 79 %




OUTPUT DISTRIBUTION

POLAR **GRAPHIC**

LED Flux: 510 Lumens at 350 mA


100



ILLUMINANCE

LED Flux: 510 Lumens at 350 mA

ILLUMINANCE VALUES AT VARIOUS DISTANCES			
RANGE	1.0 m	2.0 m	3.0 m
ILLUMINANCE	1577 Lux	394 Lux	175 Lux
MULTIPLICATOR RATE LED+LENS / LED ONLY	10 X		



All right reserved. No part of this file may be copied, reproduced in any form or by any means, electronic, mechanical, photocopying, recording or otherwise without our prior permission. DBM REFLEX 2006 www.dbmlighting.com

-100

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for LED Lighting Lenses category:

Click to view products by DBM Optix manufacturer:

Other Similar products are found below:

 $\frac{10003}{10003} \, \frac{10003/15}{10003/15} \, \frac{10003/25}{10003/L25} \, \frac{10003/L25}{10003/L25} \, \frac{10048}{10049} \, \frac{10108}{10108} \, \frac{10124}{10138} \, \frac{10140}{10192} \, \frac{10192}{10192} \, \frac{10194}{10192} \, \frac{10195}{10194} \, \frac{10196}{10195} \, \frac{10197}{10198} \, \frac{10198}{10509} \, \frac{10202}{10510} \, \frac{10202}{10510} \, \frac{10202}{10510} \, \frac{10202}{10622} \, \frac{10204}{10622} \, \frac{10204}{10628} \, \frac{10202}{10628} \, \frac{10391}{10755} \, \frac{10392}{10756} \, \frac{10395}{10757} \, \frac{10398}{10772} \, \frac{10406}{10773} \, \frac{10412}{10413} \, \frac{10414}{10415} \, \frac{10415}{10415} \, \frac{10507}{10508} \, \frac{10509}{10510} \, \frac{10511}{10620} \, \frac{10622}{10628} \, \frac{10628}{10755} \, \frac{10756}{10756} \, \frac{10757}{10758} \, \frac{10772}{10773} \, \frac{10773}{1000288} \, \frac{10003/L25}{10412} \, \frac{10196}{10412} \, \frac{10196}{10415} \, \frac$