



Desiccant in Tyvek® Pouch



Desiccant in Kraft Pouch

Tyvek® Pouch	Item Number	Pouches per Container	Pouch Size			
			Width (in)	Length (in)	Width (mm)	Length (mm)
1/6 Unit	<a href="#">1/6PLDES1200</a>	1200	2.125	2.125	54	54
1/3 Unit	<a href="#">1/3PLDES700</a>	700	2.125	2.5	54	64
1/2 Unit	<a href="#">1/2PLDES550</a>	550	2.125	2.875	54	73
1 Unit	<a href="#">1PLDES300</a>	300	3.00	4.50	76	114
1 Unit	<a href="#">1PLDES1800</a>	1800	3.00	4.50	76	114
2 Unit	<a href="#">2PLDES150</a>	150	5.00	4.50	127	114
4 Unit	<a href="#">4PLDES500</a>	500	5.00	6.250	127	159
8 Unit	<a href="#">8PLDES300</a>	300	4.50	8.50	114	216
16 Unit	<a href="#">16PLDES150</a>	150	4.50	11.00	114	279

Kraft Pouch	Item Number	Pouches per Container	Pouch Size			
			Width (in)	Length (in)	Width (mm)	Length (mm)
1/2 Unit	<a href="#">1/2KDES550</a>	550	2.375	3.50	60	89

### RoHS 2, REACH, and Conflict Minerals Statement

None of the RoHS 2 restricted materials or REACH (Registration, Evaluation and Authorization of Chemicals) substances of very high concern as of 2020/06/25, or Conflict Minerals are intentionally added in manufacturing this product. Ref: European Union Directive 2015/863/EU and Regulation (EC) No. 1907/2006/CE.

Made in North America.

Specifications and procedures subject to change without notice.

## Description

This efficient desiccant begins working by absorbing airborne moisture left inside the bag when you've finished vacuum packaging, capturing moisture that manages to pass through the bag material. Secured in a strong pouch of either clean room grade, sulphur-free, non-woven Tyvek® or economical kraft paper, desiccant helps keep your devices dry, even through unexpected shipping delays or longer than anticipated storage time.

## Specifications

### Properties

Pouch  
Unit Sizes  
Media  
Packaging

### Typical Values

Non-Woven Tyvek® or Kraft Paper  
1/6, 1/3, 1/2, 1, 2, 4, 8, 16  
Montmorillonite Clay  
Air-tight pails or drums

The recommended amount of desiccant is dependent on the interior surface area of the bag to be used. Below is a reference table indicating recommended minimum amounts of desiccant that should be used with [Moisture Barrier Bags](#). Note: number units rounded up.

As packaged SCS Desiccant in Tyvek® and Kraft pouches meets MIL-D-3464, Type I and II and is on the QPL (Qualified Product List).

INTERIOR BAG SURFACE AREA*	NUMBER OF DESICCANT UNITS		
	**MIH <20%	MIH <30%	MIH <40%
100 sq. in.	1.5	1.0	1.0
130 sq. in.	2.0	1.5	1.0
160 sq. in.	2.0	1.5	1.5
200 sq. in.	2.5	2.0	1.5
240 sq. in.	3.0	2.0	1.5
290 sq. in.	4.0	2.5	2.0
340 sq. in.	4.5	3.0	2.5
390 sq. in.	5.0	3.5	2.5
450 sq. in.	5.5	4.0	3.0
510 sq. in.	6.5	4.5	3.5
580 sq. in.	7.5	5.0	4.0
650 sq. in.	8.0	5.5	4.0
720 sq. in.	9.0	6.0	4.5

Table for recommended desiccant usage. Information taken out of EIA-583, Table 1, Page 8.

\*To measure interior bag surface area, multiply length x width x 2

\*\*MIH = Maximum Interior Humidity (%)

## DESICCANT - TYVEK® OR KRAFT PAPER POUCH

926 JR Industrial Drive, Sanford, NC 27332  
WEB SITE: [StaticControl.com](http://StaticControl.com)  
PHONE (919) 718-0000

**DRAWING NUMBER**  
DESICCANT

**DATE**  
May  
2021

## X-ON Electronics

Largest Supplier of Electrical and Electronic Components

*Click to view similar products for [Chemicals](#) category:*

*Click to view products by [Desco](#) manufacturer:*

Other Similar products are found below :

[DP-605NS](#) [3045-QT](#) [3125-9S](#) [3748-Q-58"x8"](#) [S1009-KIT-A-CS8606](#) [DP100-200ML](#) [1743-2FP](#) [152-KA-NC](#) [VERSIL406](#) [826-450G](#) [3789-Q](#) [9945](#) [7000000275](#) [1601](#) [8330-19G](#) [842AR-15ML](#) [841AR-150ML](#) [842AR-P](#) [843WB-15ML](#) [8462-85ML](#) [4354-1L](#) [838AR-P](#) [838AR-15ML](#) [419D-P-BK](#) [419D-P-GR](#) [419D-P-WH](#) [8MT-450](#) [8MT-25](#) [832HD-25ML](#) [8616-25ML](#) [832FX-450ML](#) [834ATH-375ML](#) [832HD-400ML](#) [8617-1P](#) [843AR-340G](#) [9310-300ML](#) [847-1P](#) [4228-225ML](#) [419D-55ML](#) [8800-375ML](#) [8810-375ML](#) [8820-2.55L](#) [419E-340G](#) [842UR-12ML](#) [419D-1L](#) [CW3300WHITE](#) [CW2205](#) [10447](#) [9620-945ML](#) [4140A-945ML](#)