

ESD GLOVES *Fingertips coated*
51-680-05xxB

Properties

Usage category: Clean room ISO 7-9
 Configuration: Elastic wrists
 Fabric: ■Finger tips coating
 ■Polyester 72%
 ■Spandex 11%
 ■Carbon Liner 7%
 ■PU 10%
 Surface resistance: < 10⁶ Ω
 Protection level: 1131X
 Coating: Ventilate based, polyurethane
 Colour: Grey
 Shelf life: Functional 3 years
 Washable: Not washable

Packaging: 10 pairs/bag & 25 bags/ctn

Compliance

IEC standard Conform to IEC 61-340-5-1
 CE certified: EN1149-1:2006 ; EN16350:2014
 EN 420:2003/A1(2009) ; EN388:2016
 Certificate Nr.: LEC FI00375310
 Testing body: ITS-Testing Services (UK) Limited
 Supplier item Nr.: GUT+CAP



PROTECTIVE GLOVES AGAINST
MECHANICAL RISKS
Protection levels are measured from
area of glove palm.

EN 388:2016

	A. Abrasion resistance, Min. 0; Max. 4
	B. Blade cut resistance, Min. 0; Max. 5
	C. Tear resistance, Min. 0; Max. 4
	D. Puncture resistance, Min. 0; Max. 4
	E. Blade Cut Resistance (TDM, EN ISO13997), Min. A; Max. F
	F. Impact Protection, P=Pass

Size, dimensions and part numbers

Part Number	Size	Length +/- 5 mm	Width	Border color
51-680-0502B	XXS	190 mm	80 mm	Yellow
51-680-0501B	XS	195 mm	85 mm	Pink
51-680-0500B	S	200 mm	85 mm	White
51-680-0505B	M	210 mm	90 mm	Green
51-680-0510B	L	220 mm	90 mm	Grey
51-680-0515B	XL	230 mm	95 mm	Red
51-680-0520B	XXL	240 mm	95 mm	Brown



Instructions for the maintenance and use of protective gloves:

Keep gloves away from heat and direct light, not exposed to organic solvents and their vapors. Before use, thoroughly inspect new or used gloves to ensure that they are free of defects. The gloves cannot be washed or chemically cleaned.

Warning

Do not use gloves when there is a risk of catching moving parts of the machine. The protective property only binds to the front of the glove - palm. Always use the correct size gloves and visually check their condition before each use. Never wear worn, damaged or otherwise damaged gloves. In people with sensitive skin, the possibility of skin irritation is not excluded, as the elastic cuff contains natural latex, which causes an allergic reaction in some people. In this case, do not continue to use gloves and seek professional help.

Note

The specified level of protection, according to EN 388, can help with the selection of the glove, but it is important to note that the application conditions cannot be simulated in a laboratory, and it is the responsibility of the user, not the manufacturer, to approve the application in specific conditions (working operation).

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Eurostat manufacturer:

Other Similar products are found below :

[20-007-0305](#) [20-007-0406](#) [20-007-0508](#) [20-007-0608](#) [20-007-0610](#) [20-007-0810](#) [20-007-0812](#) [20-007-0816](#) [20-007-1012](#) [20-007-1216](#) [20-007-1620](#) [20-008-0305](#) [20-008-0406](#) [20-008-0610](#) [20-008-0812](#) [20-008-1012](#) [20-008-1216](#) [20-010-0006](#) [20-010-0007](#) [20-011-0305](#) [20-011-0406](#) [20-011-0608](#) [20-011-0610](#) [20-011-0812](#) [20-011-1214](#) [20-011-1216](#) [20-011-1620](#) [20-011-1824](#) [20-012-0305](#) [20-012-0406](#) [20-012-0508](#) [20-012-0610](#) [20-012-0810](#) [20-012-0812](#) [20-012-1012](#) [20-012-1216](#) [20-013-0003](#) [20-014-0002](#) [20-014-0006](#) [20-019-6029](#) [20-053-0006](#) [20-053-0035](#) [20-053-0070N](#) [20-053-0560](#) [20-054-0002](#) [20-054-0003](#) [20-062-0031](#) [20-063-0011](#) [20-071-0430](#) [20-071-0816](#)