

2600  
2650  
2680  
2700



● ● ● Price index

IPA Qualification Certificate Air Cleanless Class ISO Class 3 (at v = 2 m/s) upon request

ESD classification: Electrically conductive ESD/ATEX version upon request

UL94 V2 classifications upon request



Snap-open mechanism, choice of snap-open on left or right. Hinged crossbar can be swiveled by more than 180° on both sides. Lightning-fast closing by hand. Secure fit without additional locking devices.



When to use the Series 2600/2650/2680/2700:

- Snap-open accessibility along both radii
- If integrated strain relief is required at the connection point
- Modular interior separation
- If long service life is required
- If easy installation is required
- If half E-Tube is required (Series 2650)
- If fully enclosed E-Tube is required (Series 2680)




When not to use it:

- If maximum stability is required  
▶ System E4.1, Series E4.32, page 7.34
- If the application is very simple  
▶ Easy Chain®, Series E26, page 3.46
- E-Tubes with small bending radii 075  
▶ E2 E-Tubes, Series R58, page 6.34

E2/000 | Series 2600 · 2650 · 2680 · 2700



- ❶ Opening system for rapid opening, either from the right or the left
- ❷ Double stop dog for long unsupported length
- ❸ Cross bars with high locking range
- ❹ Lateral glide surfaces for side-mounted operation
- ❺ Tried-and-tested mounting bracket
- ❻ Integrated strain relief possible
- ❼ Half E-Tube Series 2650
- ❽ Series 2600 and 2650 snap-open along inner radius
- ❾ Fully enclosed E-Tube Series 2680
- ❿ Modular interior separation
- ⓫ Easy assembly by optimized pin
- ⓬ Also available as ESD version
- ⓭ **Strain relief separator** - Separator with integrated strain relief ▶ page 5.124



Order example complete E-Chain®

Please indicate chain-lengths or number of links Example: 3 m or 54 links

3 m 2700.10.100.0

E-Chain®

with 2 separators 261 assembled every 2<sup>nd</sup> link

Interior separation

1 set 2610.34PZB

Mounting bracket

5.114





Available from stock. Delivery in 24h or today! (Delivery time means time until shipping of goods)

E2/000 | Series 2600 · 2650 · 2680 · 2700 | Dimensions and Technical Data



**Unsupported length**


$FL_G$  = with straight upper run  
 $FL_B$  = with permitted sag  
 Further information ► Design, page 1.12



- $S$  = Length of travel
- $R$  = Bending radius
- $H$  = Nominal clearance height
- $H_F$  = Required clearance height
- $H_{in}$  = Trough inner height
- $D$  = Overlength E-Chain\* radius in final position
- $K = \pi \cdot R + \text{"safety"}$
- $D_2$  = Overlength - long travels, gliding
- $K_2$  = \*Further add-on
- $H_2$  = \*Mounting height
- \*if the mounting bracket location is set lower

**Other installation methods**


- Vertical, hanging  $\leq 50$  m
- Vertical, standing  $\leq 3$  m
- Side mounted, un supp.  $\leq 1$  m
- Rotary requires further calculation
- Unsupported length of upper run = upon request



**Short travels - unsupported**

Unsupported E-Chains\* feature positive camber over short travels. This must be accounted for when specifying the clearance height  $H_F$ . Please consult igus\* if space is particularly restricted.

The required clearance height:  
 $H_F = H + 35$  mm  
 (with 2,0 kg/m fill weight)




Pitch = 56 mm/link    Links/m = 18 (1008 mm)    Chain length =  $S_2 + K$

	063*	075*	100	125	150	175	200	250
$H$	180	200	250	300	350	400	450	550
$D$	140	150	175	200	225	250	275	325
$K$	335	375	475	550	650	750	825	925
$H_2$	180	200	166	166	166	166	166	166
$D_2^{*25}$	140	150	350	475	500	655	770	950
$K_2$	335	375	616	784	896	1120	1288	1624

\*for Series 2650/2680 upon request

Long travel lengths from 10 m to max. 120 m    Chain length =  $S_2 + K_2$



In case of travels between 4 and 10 m we recommend a longer unsupported length.



**Gliding, long travel applications (max. 120 m)**

In this case the E-Chain\* upper run will be introduced in a guide trough on the lower run. We recommend to realize the engineering of such a plant by our technicians.

**Technical Data**

Speed / acceleration $FL_G$	max. 20 [m/s] / max. 200 [m/s <sup>2</sup> ]
Speed / acceleration $FL_B$	max. 3 [m/s] / max. 6 [m/s <sup>2</sup> ]
Gliding speed / acceleration (maximum)	max. 10 [m/s] / max. 50 [m/s <sup>2</sup> ]
Material - permitted temperature °C	igumid G / -40° up to +120° C
Flammability class, igumid G	VDE 0304 IIC UL94 HB



Details of material properties  
 ► page 1.38

For support of the lower run - **Support Tray tool kit** available ► page 9.70

2600  
2650  
2680  
2700

35

E2/000 medium  
Inner height: 35 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222



► page 5.91

5.115

2600  
2700


igus® E-ChainsSystems®

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)

5.116



Part No. structure

2600. 05. 063. 0



E2/000 | E-Chains® | Series 2600·2700 | Product Range

Series 2600 - E-Chain® - snap-open along inner radius


Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii								Weight [kg/m]
2600.05.□.0	50	66	063	075	100	125	150	175	200	250	≈ 1,17	
2600.06.□.0	65	81	063	075	100	125	150	175	200	250	≈ 1,24	
2600.07.□.0	75	91	063	075	100	125	150	175	200	250	≈ 1,30	
2600.09.□.0	90	106	063	075	100	125	150	175	200	250	≈ 1,37	
2600.10.□.0	100	116	063	075	100	125	150	175	200	250	≈ 1,39	
2600.12.□.0	125	141	063	075	100	125	150	175	200	250	≈ 1,48	
2600.15.□.0	150	166	063	075	100	125	150	175	200	250	≈ 1,62	
2600.17.□.0	175	194	063	075	100	125	150	175	200	250	≈ 1,85	

Supplement Part No. with required radius. Example: 2600.05.063.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link · Links/m = 18



Please note: For using this series for long travels (gliding), please consult with igus® first. For long travels, igus® specifies E-Chains® that snap open on the outer radius.



Part No. structure

2700. 05. 063. 0



**Standard** Series 2700 - E-Chain® - snap-open along outer radius - Standard!

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii								Weight [kg/m]
2700.05.□.0	50	66	063	075	100	125	150	175	200	250	≈ 1,17	
2700.06.□.0	65	81	063	075	100	125	150	175	200	250	≈ 1,24	
2700.07.□.0	75	91	063	075	100	125	150	175	200	250	≈ 1,30	
2700.09.□.0	90	106	063	075	100	125	150	175	200	250	≈ 1,37	
2700.10.□.0	100	116	063	075	100	125	150	175	200	250	≈ 1,39	
2700.12.□.0	125	141	063	075	100	125	150	175	200	250	≈ 1,48	
2700.15.□.0	150	166	063	075	100	125	150	175	200	250	≈ 1,62	
2700.17.□.0	175	194	063	075	100	125	150	175	200	250	≈ 1,85	

Supplement Part No. with required radius. Example: 2700.05.063.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link · Links/m = 18



E2/000 | E-Tubes | Series 2650·2680 | Product Range



Series 2650 - half E-Tube - snap-open along inner radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
2650.05. .0	50	66	100	125 150 175 200 250	≈ 1,25
2650.06. .0	65	81	100	125 150 175 200 250	≈ 1,36
2650.07. .0	75	91	100	125 150 175 200 250	≈ 1,40
2650.09. .0	90	106	100	125 150 175 200 250	≈ 1,55
2650.10. .0	100	116	100	125 150 175 200 250	≈ 1,61
2650.12. .0	125	141	100	125 150 175 200 250	≈ 1,70
2650.15. .0	150	166	100	125 150 175 200 250	≈ 1,80
2650.17. .0	175	194	100	125 150 175 200 250	≈ 2,00



The widths **Bi 90/150/175** are available upon request. Time of delivery approx. 6-8 weeks after order.  
The bending radii **063 075** are available upon request.

Supplement Part No. with required radius. Example: 2650.05.100.0


0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18



Please note: For using this series for long travels (gliding), please consult with igus® first. For long travels, igus® specifies E-Chains® that snap open on the outer radius.



Part No. structure



Series 2680 - E-Tube - snap-open along inner radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
2680.05. .0	50	66	100	125 150 175 200 250	≈ 1,33
2680.06. .0	65	81	100	125 150 175 200 250	≈ 1,43
2680.07. .0	75	91	100	125 150 175 200 250	≈ 1,51
2680.09. .0	90	106	100	125 150 175 200 250	≈ 1,62
2680.10. .0	100	116	100	125 150 175 200 250	≈ 1,81
2680.12. .0	125	141	100	125 150 175 200 250	≈ 1,99
2680.15. .0	150	166	100	125 150 175 200 250	≈ 2,17
2680.17. .0	175	194	100	125 150 175 200 250	≈ 2,35



The widths **Bi 65/90/150/175** are available upon request. Time of delivery approx. 6-8 weeks after order.  
The bending radii **063 075** are available upon request.

Supplement Part No. with required radius. Example: 2680.07.100.0


0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18



Please note: For using this series for long travels (gliding), please consult with igus® first. For long travels, igus® specifies E-Chains® that snap open on the outer radius.



Part No. structure




For smaller bending radii we recommend the fully closed E-Tubes, Series R58 ▶ page 6.34

2650  
2680

E2/000 medium  
Inner height: 35 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222



▶ page 5.91

2600  
2650  
2680  
2700

igus® E-ChainsSystems®

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne

Internet: www.igus.eu  
E-mail: info@igus.de

5.118



**Vertical Separator**

unassembled	260
assembled	261



**Vertical Separator\***

unassembled	260.24
assembled	261.24



**Spacer\***

unassembled	205.09
assembled	215.09



**Strain Relief Separator**

unassembled	262.Z
assembled	263.Z



\*For side-mounted applications

**Vert. Separator, slotted**

unassembled	268
assembled	269



**Full-Width Shelf**

X-1	
t=2,5	

**Middle Plate**

unassembled	262
assembled	263



**Slotted Separator**

unassembled	266
assembled	267



**Slotted Separator, open**

unassembled	276
assembled	277



**Side Plate**

unassembled	264
assembled	265



**Shelf**


X	
X-7	
t=2,5	

E2/000 | E-Chains® | Series 2600·2700 | Interior Separation

**Option 1: Vertical Separators and Spacer for E-Chains®**

Vertical Separators are used if a vertical subdivision of the E-Chain® interior is required - By standard Vertical Separators are assembled every other E-Chain® link



- Standard subdivision (Series 2600/Series 2700) with Vertical Separator 261, for combinations with Full-Width Shelf 221.X
- If a broad distance shall be kept between the separators or they have to be fixed in their position, e.g. in case of side mounted applications, separators with wide base 261.24 or Spacer 215.09 can be used
- Strain Relief Separator 262.Z, integrable in the mounting bracket, to position at any point



**Option 2: Full-Width Shelves for E-Chains®**

For applications involving many thin cables with similar or identical diameters

- Vertical Separator, slotted 269 - for applications with Full-Width Shelf 221.X




Width X [mm]	Part No. unassembled	Part No. assembled
050	220.50	221.50
065	220.65	221.65
075	220.75	221.75
090	220.90	221.90

Width X [mm]	Part No. unassembled	Part No. assembled
100	220.100	221.100
125	220.125	221.125
150	220.150	221.150
175	220.175	221.175

**Option 3: Shelves for E-Chains®**

For applications involving many cables with different diameters. The Shelves can be arranged elevator-shifted with different bottoms within the entire E-Chain® width

- Shelf 2210.X can be combined with Middle Plate 263, Slotted Separator 267 and Side Plate 265
- Option 3 "Shelves" can also be combined with option 1 "Vertical Separators"
- Assembling of the Slotted Separator, open 277 in the existing separation afterwards possible



Width X [mm]	Part No. unassembled	Part No. assembled
018	2200.18	2210.18
023	2200.23	2210.23
028	2200.28	2210.28
033	2200.33	2210.33
038	2200.38	2210.38
043	2200.43	2210.43
048	2200.48	2210.48

Width X [mm]	Part No. unassembled	Part No. assembled
058	2200.58	2210.58
068	2200.68	2210.68
073	2200.73	2210.73
088	2200.88	2210.88
099	2200.99	2210.99
124	2200.124	2210.124
149	2200.149	2210.149

Info ► www.igus.de/en/2600 · www.igus.de/en/2650 · www.igus.de/en/2680 · www.igus.de/en/2700

## E2/000 | E-Tubes | Series 2650·2680 | Interior Separation




2600  
2650  
2680  
2700

### Option 4: Vertical Separators for E-Tubes

Vertical Separators are used if a vertical subdivision of the E-Tube interior is required -  
By standard Vertical Separators are assembled every other E-Tube link

- Standard subdivision of the half E-Tube (Series 2650) and the fully enclosed E-Tube (Series 2680) with Vertical Separator, slotted 26511, for combinations with Full-Width Shelf 221.X


Vert. Separator, slotted		
unassembled	26501	
assembled	26511	



### Option 5: Full-Width Shelves for E-Tubes

For applications involving many thin cables with similar or identical diameters

- Vertical Separator, slotted 26511 - for applications with Full-Width Shelf 221.X



Width X [mm]	Part No. unassembled	Part No. assembled
050	220.50	221.50
065	220.65	221.65
075	220.75	221.75
090	220.90	221.90

Width X [mm]	Part No. unassembled	Part No. assembled
100	220.100	221.100
125	220.125	221.125
150	220.150	221.150
175	220.175	221.175


Full-Width Shelf
X - 1
t = 2,5

### Variante 6 - Shelves for E-Tubes

For applications involving many cables with different diameters. The Shelves can be arranged elevator-shifted within the entire E-Chain® width

- Shelf 2210.X can be combined with Vertical Separator, slotted 26511
- Assembling of the Slotted Separator, open 277 in the existing separation afterwards possible

Slotted Separator, open		
unassembled	276	
assembled	277	



Width X [mm]	Part No. unassembled	Part No. assembled
018	2200.18	2210.18
023	2200.23	2210.23
028	2200.28	2210.28
033	2200.33	2210.33
038	2200.38	2210.38
043	2200.43	2210.43
048	2200.48	2210.48

Width X [mm]	Part No. unassembled	Part No. assembled
058	2200.58	2210.58
068	2200.68	2210.68
073	2200.73	2210.73
088	2200.88	2210.88
099	2200.99	2210.99
124	2200.124	2210.124
149	2200.149	2210.149

Shelf
X
X - 7
t = 2,5

Info ► [www.igus.de/en/2600](http://www.igus.de/en/2600) · [www.igus.de/en/2650](http://www.igus.de/en/2650) · [www.igus.de/en/2680](http://www.igus.de/en/2680) · [www.igus.de/en/2700](http://www.igus.de/en/2700)

E2 medium  
Inner height: 35 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222




► page 5.91

5.119




2600  
2650  
2680  
2700

**igus® Series 2600 · 2650 · 2680 · 2700 | Accessories | Mounting Brackets, Polymer**




Possible installation conditions for assembled mounting brackets ▶ Order example "preassembled" below




**The Standard - option polymer - pivoting**

- Recommended for unsupported and gliding applications
- Well suited for tight installation conditions
- Strain relief with detachable tiwrap plates
- Variable traverse angle for flexible assembly
- The twistability of the E-Chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options


Moving end with bore (outer link) 26...3PZ(B)



26...4PZ(B) Fixed end with pin (inner link)




Possible installation conditions for assembled mounting brackets ▶ Order example "preassembled" below



**Option polymer - locking**

- Recommended for unsupported and gliding applications
- At very high speed and/or acceleration
- If space is limited for height (the  $H_F$  measurement)
- The twistability of the E-Chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options

Moving end with bore (outer link) 26...1PZ(B)



26...2PZ(B) Fixed end with pin (inner link)

**Dimensions and order configurations**

Strain relief is possible on the moving end and/or the fixed end.

**Part No. structure (pivoting)**

2605.	34	PZB	A1	
-------	----	-----	----	--

A... must be indicated on preassembled configurations  
With assembled strain relief tiwrap plates  
Full set pivoting = 34  
Mounting brackets for selected chain type

- Full set, for both ends:**  
2605. 34 PZB +tiwrap plate
- Single-part order:**  
2605. 3 PZB +tiwrap plate
- Mounting bracket **with bore**  
2605. 4 PZB +tiwrap plate
- Mounting bracket **with pin**

**Part No. structure (locking)**


2605.	12	PZB	A1	
-------	----	-----	----	--

A... must be indicated on preassembled configurations  
With assembled strain relief tiwrap plates  
Full set locking = 12  
Mounting brackets for selected chain type

- Full set, for both ends:**  
2605. 12 PZB +tiwrap plate
- Single-part order:**  
2605. 1 PZB +tiwrap plate
- Mounting bracket **with bore**  
2605. 2 PZB +tiwrap plate
- Mounting bracket **with pin**

26...3PZ(B) Standard! (pivoting)  
26...1PZ(B) (locking)

Moving end



Standard! (pivoting) 26...4PZ(B)  
(locking) 26...2PZ(B)

Fixed end

For E-Chain®	Part No. full set with tiwrap plate	Part No. with tiwrap plate + 10 cable tiwraps	Part No. full set without tiwrap plate	Dim. A [mm]
2600 - 2700.05 ▶	2605. [ ] PZB	2605. [ ] PZBK1	2605. [ ] PZ	30
2600 - 2700.06 ▶	2606. [ ] PZB	2606. [ ] PZBK1	2606. [ ] PZ	45
2600 - 2700.07 ▶	2607. [ ] PZB	2607. [ ] PZBK1	2607. [ ] PZ	55
2600 - 2700.09 ▶	2609. [ ] PZB	2609. [ ] PZBK1	2609. [ ] PZ	70
2600 - 2700.10 ▶	2610. [ ] PZB	2610. [ ] PZBK1	2610. [ ] PZ	80
2600 - 2700.12 ▶	2612. [ ] PZB	2612. [ ] PZBK1	2612. [ ] PZ	105
2600 - 2700.15 ▶	2615. [ ] PZB	2615. [ ] PZBK1	2615. [ ] PZ	130
2600 - 2700.17 ▶	2617. [ ] PZB	2617. [ ] PZBK1	2617. [ ] PZ	155

Please add the Part No. with the requested index - 34 for the pivoting configuration

e.g. 2605. 34 PZB or 12 for the locking configuration e.g. 2605. 12 PZB

For the preassembled mode please add the index A1...A4 e.g. 2605. 34 PZB A1

igus® GmbH  
51147 Cologne

Internet: www.igus.eu  
E-mail: info@igus.de

5.120

Info ▶ [www.igus.de/en/2600](http://www.igus.de/en/2600) · [www.igus.de/en/2650](http://www.igus.de/en/2650) · [www.igus.de/en/2680](http://www.igus.de/en/2680) · [www.igus.de/en/2700](http://www.igus.de/en/2700)

Series 2600 · 2650 · 2680 · 2700 | Accessories | Mounting Brackets, Steel




2600  
2650  
2680  
2700




**Steel mounting bracket - locking**

- Locked connections
- One part for all chain widths
- Electrically conductive
- Bolted connection outside of chain cross-section possible


Moving end with bore  
(outer link) 260.1



260.2 Fixed end  
with pin (inner link)



Possible installation conditions -  
Further installation angles ► installation sketch



**Dimensions and order configurations**

\*pivoting with no stop, (360°)

For E-Chain*	Part No. full set	Dim. A [mm]	Dim. B [mm]
2600 - 2700.05 ►	260. 12	37	83
2600 - 2700.06 ►	260. 12	52	98
2600 - 2700.07 ►	260. 12	62	108
2600 - 2700.09 ►	260. 12	77	123
2600 - 2700.10 ►	260. 12	87	133
2600 - 2700.12 ►	260. 12	112	158
2600 - 2700.15 ►	260. 12	137	183
2600 - 2700.17 ►	260. 12	163	209

260. 12 Full set, 4 parts  
2 with pin / 2 with bore

**Single-part order:**  
260. 1 Mounting bracket  
with bore, 1 part left / right  
260. 2 Mounting bracket with  
pin, 1 part left / right

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222




► page 5.91




2600  
2650  
2680  
2700

**igus® E-Chains® | Series 2600·2700 | Accessories | Mounting Brackets, KMA**



The attachment variants arising automatically by the choice of the KMA mounting bracket




**Option KMA, pivoting for E-Chains® Series 2600 and Series 2700**

- Recommended for unsupported applications
- Bolted connection outside of chain cross-section
- Confined installation conditions
- Universal mountable with attachment capability on all sides
- Stackable


**Moving end with bore**

Series 2600 = 26001...1  
Series 2700 = 26001...1




Series 2600 = 26001...2  
Series 2700 = 26001...2

**Fixed end with pin**



The attachment variants arising automatically by the choice of the KMA mounting bracket




KMA = Polymer Metal Mounting Bracket

**Option KMA, locking for E-Chains® Series 2600 and Series 2700**

- Recommended for vertical hanging / standing applications
- Bolted connection outside of chain cross-section
- At very high speed and acceleration
- Universal mountable with attachment capability on all sides
- Stackable

**Moving end with bore**

Series 2600 = 26101...1  
Series 2700 = 26101...1




Series 2600 = 26101...2  
Series 2700 = 26101...2

**Fixed end with pin**

**Dimensions and order configurations**

**Part No. structure (pivoting)**

26001.05.12.CA



**Full set, for both ends:**

26001.05.12.C (with C-profile)

**Single-part order:**

26001.05.1.C (with C-profile)

Mounting bracket with bore

26001.05.2.C (with C-profile)

Mounting bracket with pin

**Part No. structure (locking)**

26101.05.12.CA



**Full set, for both ends:**

26101.05.12.C (with C-profile)

**Single-part order:**

26101.05.1.C (with C-profile)

Mounting bracket with bore

26101.05.2.C (with C-profile)

Mounting bracket with pin

2600 | 2700 = 26001...1 (pivoting)


2600 | 2700 = 26101...1 (locking)

2600 | 2700 = 26001...2 (pivoting)

2600 | 2700 = 26101...2 (locking)

**Moving end**

**Fixed end**



For E-Chain®	Part No. full set with C-profile	Part No. full set without C-profile	Dim. A [mm]	Dim B [mm]
Series 2600/2700				
2600/2700.05	26001.05.12.C	26001.05.12	58	69
2600/2700.06	26001.06.12.C	26001.06.12	73	84
2600/2700.07	26001.07.12.C	26001.07.12	83	94
2600/2700.09	26001.09.12.C	26001.09.12	98	109
2600/2700.10	26001.10.12.C	26001.10.12	108	119
2600/2700.12	26001.12.12.C	26001.12.12	133	144
2600/2700.15	26001.15.12.C	26001.15.12	158	169
2600/2700.17	26001.17.12.C	26001.17.12	183	194

● For **E-Chains®** please add the Part No. with the requested index

For the pivoting option e.g. 26001.05.12 or for the locking option e.g. 26101.05.12

For the **preassembled** mode please add the index [A], e.g. 26101.05.12 [A]

igus® GmbH  
51147 Cologne

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)


5.122

Info ► [www.igus.de/en/2600](http://www.igus.de/en/2600) · [www.igus.de/en/2650](http://www.igus.de/en/2650) · [www.igus.de/en/2680](http://www.igus.de/en/2680) · [www.igus.de/en/2700](http://www.igus.de/en/2700)

E-Tubes | Series 2650·2680 | Accessories | Mounting Brackets, KMA



2600  
2650  
2680  
2700




KMA = Polymer Metal Mounting Bracket

**Option KMA, pivoting for half E-Tubes Series 2650 and for full E-Tubes Series 2680**

- Recommended for unsupported applications
- Bolted connection outside of chain cross-section
- Confined installation conditions
- Universal mountable with attachment capability on all sides
- Stackable

**Moving end with bore**

Series 2650 = 26500...1  
Series 2680 = 26800...1





Series 2650 = 26500...2  
Series 2680 = 26800...2

**Fixed end with pin**



The attachment variants arising automatically by the choice of the KMA mounting bracket




KMA = Kunststoff-Metall-Anschlusselement

**Option KMA, locking for half E-Tubes Series 2650  
Option KMA, locking for full E-Tubes Series 2680**

- Recommended for vertical hanging / standing applications
- Bolted connection outside of chain cross-section
- At very high speed and acceleration
- Universal mountable with attachment capability on all sides
- Stackable

**Moving end with bore**

Series 2650 = 26510...1  
Series 2680 = 26810...1




Series 2650 = 26510...2  
Series 2680 = 26810...2

**Fixed end with pin**



The attachment variants arising automatically by the choice of the KMA mounting bracket




2650 = 26500...1 | 2680 = 26800...1 (pivoting)  
2650 = 26510...1 | 2680 = 26810...1 (locking)

2650 = 26500...2 | 2680 = 26800...2 (pivoting)  
2650 = 26510...2 | 2680 = 26810...2 (locking)

**Moving end**

**Fixed end**




For E-Chain*	Part No. full set	Part No. full set	Dim. A [mm]	Dim B [mm]
Series 2650/2680	<b>with C-profile</b>	<b>without C-profile</b>		
2650/2680.05	...05.12.C	...05.12	58	69
2650/2680.06	...06.12.C	...06.12	73	84
2650/2680.07	...07.12.C	...07.12	83	94
2650/2680.09	...09.12.C	...09.12	98	109
2650/2680.10	...10.12.C	...10.12	108	119
2650/2680.12	...12.12.C	...12.12	133	144
2650/2680.15	...15.12.C	...15.12	158	169
2650/2680.17	...17.12.C	...17.12	183	194

- For **half E-Tube** please add the Part No. with the requested index  
For the pivoting option e.g. [26500].05.12 or for the locking option e.g. [26510].05.12  
For the **preassembled** mode please add the index [A] e.g. [26510].05.12[A]
- For **full E-Tube** please add the Part No. with the requested index  
For the pivoting option e.g. [26800].05.12 or for the locking option e.g. [26810].05.12  
For the **preassembled** mode please add the index [A] e.g. [26810].05.12[A]

**Maße und Bestellvarianten**

**Part No. structure (pivoting)**



**Full set, for both ends:**

[26800].05.12.C (with C-profile)

**Single-part order:**


[26800].05.1.C (inkl. C-Profil)

Mounting bracket **with bore**

[26800].05.2.C (inkl. C-Profil)

Mounting bracket **with pin**

**Part No. structure (locking)**



**Full set, for both ends:**

[26810].05.12.C (with C-profile)

**Single-part order:**

[26810].05.1.C (with C-profile)

Mounting bracket **with bore**

[26810].05.2.C (with C-profile)

Mounting bracket **with pin**

2600  
2650  
2680  
2700

igus® E-ChainSystems®





E2/000 | Series 2600 · 2650 · 2680 · 2700 | Accessories | Strain Relief



### Tiewrap plate as individual part

As individual component screwed on KMA. Can be plugged in the mounting brackets. **Details ▶ chapter 10**



Tiewrap plate	No. of teeth n	Dim. C [mm]	Dim. B [mm]
3050.ZB	5	50	30
3075.ZB	7	75	55
3100.ZB	10	100	80
3115.ZB	11	115	95
3125.ZB	12	125	105
3150.ZB	15	150	130
3175.ZB	17	175	155
3200.ZB	20	200	180
3225.ZB	22	225	205
3250.ZB	25	250	230

(- = no / + = yes)

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222



### Cable tiewraps as individual part

Cable tiewraps (100-piece bag)	Width x length	max. Ø	Tensile strength
CFB.001	4,8 x 150 mm	36 mm	222 N




### "Double" strain relief

If an E-Chain® is harnessed with a very large number of cables, strain relief may be necessary at two levels. Our 2050.Z strain relief system was developed for this purpose. It can be placed in any position along the E-Chain®. As required, the 2050.Z strain relief system is simply clamped onto the crossbar of the chain link. No additional installation elements are needed. **Details ▶ chapter 10**

Part No.	Width strain relief [mm]	
2050.Z*	60	*not available for Series 2650/2680

igus® GmbH  
51147 Cologne



### Strain relief separator

Separator with integrated strain relief, for use in the first or last chain link. For manufacturing of switchgear cabinets or for the assembly of machines. Easy to assemble without any fastening device. Separator base 262.Z is 10 mm wide. The possible number of separators per E-Chain® is defined by its inner width *Bi* and by the cable-diameter. **Details ▶ chapter 10**

Part No.	Number of teeth	For Series
262.Z	3 one side	2600/2700 E-Chain®



### Strain relief for steel mounting brackets

Clip-on connection is not possible with steel mounting brackets. In this case, the tiewrap plates must be bolted directly into separate bore holes in front of the mounting bracket. Alternatively the tiewrap plates 30XX.Z and ZS can be also used here. **Details ▶ chapter 10**

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)



Other strain relief elements - optional ▶ chapter 10

### Chainfix strain relief C-profile-solutions - more Details ▶ chapter 10

Chainfix clamps made of steel or stainless steel	Chainfix Clips - modular, snap-on	Chainfix Nugget with pre-harnessed cable strap	Chainfix - tiewrap plates with clip-on connection


5.124

Info ▶ [www.igus.de/en/2600](http://www.igus.de/en/2600) · [www.igus.de/en/2650](http://www.igus.de/en/2650) · [www.igus.de/en/2680](http://www.igus.de/en/2680) · [www.igus.de/en/2700](http://www.igus.de/en/2700)

Part No. 972.30 | 972.32 | Trough height: 117 mm  
 Aluminum "SuperTrough" | Basic Version



2600  
 2650  
 2680  
 2700



- $B_a$  = Outer width E-Chains® / E-Tube
- $B_i$  = Inner width E-Chains® / E-Tube
- $h_a$  = Outer height E-Chains® / E-Tube
- $H_{Ri}$  = Inner trough height
- $H_{Ra}$  = Outer trough height
- $B_{Ri}$  = Inner trough width ► depends on dim.  $B_a$
- $B_{Ra}$  = Outer trough width
- $n_{Mon}$  = Number of installation sets (left/right)
- $n_{Ri}$  = Number of trough sets (left/right)
- !  $H_{Ri} \geq 2 \cdot h_a$
- !  $B_{Ri} \geq B_a + 4$
- = Guide trough set    ● = Glide bar
- = Installation set "Basic"    ● = C-Profile

Installation set "Basic" with C-Profile

Bottom Clamp attached optionally inwards or outwards

2700.05.200.0 ► Order example


$B_{Ri}$ [mm]	Part No.	
	attached inwards	attached outwards
.05	70	960.30.175
.06	85	960.30.150 960.30.200
.07	95	960.30.150 960.30.200
.09	110	960.30.175 960.30.225
.10	120	960.30.175 960.30.225
.12	145	960.30.200 960.30.250
.15	170	960.30.225 960.30.275
.17	198	960.30.250 960.30.300



- Components, trough "Basic": ① Trough side parts, aluminum, 2 m ② Glide bar, plastic, 2 m ③ Glide strips, plastic, 2 m (without glide strips on request) ⑩ Optional: Silencer profile, rubber
- Components, installation set "Basic": ④ Bottom clamp, aluminum ⑤ C-profile, steel galvanized ⑥ Screw M6 x16 ⑦ Sliding nut M6 ⑧ Interface connector, plastic

Order example: Length of travel 30 m - Center mounted for Series 2700.06.200.0 with  $B_{Ri} = 85$

- Guide trough set (set of 2 trough side parts, incl. glide strips) **without** glide bar  
 Order text: 16 m guide trough without glide bar (8 x 2 m sections) Part No. 972.30.SL
- Guide trough set (set of 2 trough side parts, incl. glide strips) **with** glide bar  
 Order text: 16 m guide trough with glide bar (8 x 2 m sections) Part No. 972.32.SL
- Installation set "Basic" complete (guide trough-sets + 1) Part No. 960.30.150
- Order text: 17 installation sets "Basic"
- Module for the fixed end  
 Order text: 1 set Part No. 972.81
- Option: For an additional noise dampening with silencer profile, please add Index A - Example: Part No. 972.30.SLA



Principle sketch: Number of installation sets to be installed = Number of trough sections + 1



**A quick fix for mounting the stationary end of an E-Chain®**  
 With this module for the fixed end, fast and easy mounting onto the Aluminum "SuperTrough" is now possible without any drilling. Fast mounting of the E-Chain® by clamping onto the aluminum trough

- Quick relocation of the stationary end
- No drilling necessary

Details about Alu "SuperTrough" and further guidance possibilities ► chapter 9, guide troughs

Phone +49- (0) 22 03-96 49-800  
 Fax +49- (0) 22 03-96 49-222



5.125

## X-ON Electronics

Largest Supplier of Electrical and Electronic Components

*Click to view similar products for [Cable Mounting & Accessories](#) category:*

*Click to view products by [Iigus](#) manufacturer:*

Other Similar products are found below :

[HP-4N](#) [582603-1](#) [009333-000](#) [727844N003](#) [809090N001](#) [8109](#) [843188-000](#) [843459N001](#) [843460N003](#) [8666](#) [967279N002](#) [GPQC1/0](#) [DB-11](#) [1300830208](#) [1300840039](#) [1300900026](#) [1300990052](#) [1301740005](#) [1301800121](#) [1301800416](#) [1300830184](#) [1300990149](#) [1301580036](#) [1301720103](#) [1301720135](#) [1301720152](#) [1301720157](#) [1301740009](#) [1301770011](#) [1301850553](#) [1301860939](#) [1302000074](#) [1302264431](#) [1337706-2](#) [APA18-AK](#) [MTX6UTPSRC-C](#) [1-787307-1](#) [185491N001](#) [HP-6N](#) [C-202-C](#) [202C221-13-0](#) [OMTM-S10-C0](#) [205339-4](#) [CA7308-000](#) [8S23-75FR-CS8184](#) [2684](#) [9648](#) [3089](#) [988382-000](#) [A0270164](#)