

ECG.1B.307.CYM

SUMMARY

Wires

Low voltage



Image is for illustrative purpose only

| Series | 1B | | |
|------------------|--------------------|--|--|
| Termination type | Female crimp | | |
| IP rating | 50 | | |
| AWG wire size | 26.00 - 22.00 | | |
| Cable Ø | 0.00 - 0.00 mm | | |
| Status | active | | |
| Matching parts | FGG.1B.307.CYCD42Z | | |

7

Download

Request a quote Catalog

TECHNICAL DETAILS

Mechanics

| Shell Style/Model | EC*: Fixed receptacle with two nuts (back panel mounting) |
|-------------------|---|
| Keying | 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Housing Material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight | 11.90 g |
| Performance | |
| Configuration | 1B.307 : 7 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated Current | 7 Amps |
| | |

Specifications

Contact Type: Crimp Contact Retention: 22 N Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in) Min. Conductor: 0.14 mm^2 (AWG 26) Max. Conductor: 0.34 mm^2 (AWG 22) R (max): 6.1 mOhm Vtest (contact-shell): 1450 V (AC), 2050 V (DC)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

Endurance (Shell): 5000 Temp (min / max): -55°C / +250°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS







Dimensions

| | А | В | E | L | Μ | N | S1 | \$3 | e |
|-----|------|------|------|------|------|------|------|------|---------|
| mm. | 16 | 15.8 | 6 | 23 | 3.5 | 21.1 | 10.5 | 14 | M12x1.0 |
| in. | 0,63 | 0,62 | 0,24 | 0,91 | 0,14 | 0,83 | 0,41 | 0,55 | |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

| Crimp Tool: | DPC.91.701.V |
|----------------------|-------------------------------|
| Crimp settings: | AWG/Selector = 22-24-26/6-5-5 |
| Positionner: | DCE.91.071.BVM |
| Extractor: | DCF.91.070.2LT |
| Spanner 2: | DCH.91.161.PA |
| Replacement contact: | EGG.1B.655.ZZM |

Cables

| CMN.07.T26.037QGZE | TPR (medical) | Grey | |
|--------------------|---------------|-------|-------------|
| CMN.07.T28.044PGZE | | Grey | |
| CMN.07.T28.044PNZE | | | |
| 270250 | PVC | Grey | |
| 70140 | PVC | Grey | |
| 7041 | PVC | Grey | > |
| 7050 | PVC | Black | > |
| 717920 | PVC | Grey | € |
| CTR.75.030.121875G | PVC | Grey | € |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Circular Push Pull Connectors category:

Click to view products by LEMO manufacturer:

Other Similar products are found below :

6407-249V-11273P 6408-201V-13273 6408-202V-13343 6408-202V-17343 EZG.0B.309.CLN FFA.2S.310.ZLA FGA.1B.307.CYCD72Z FGJ.1B.304.CLLD76 FGJ.1B.306.CWLD72 FGJ.3B.304.CYMD10Z FGJ.3B.304.CYMD82Z PCS.01.250.DLLE24 PHG.0K.305.CYMC40Z PHG.1K.308.CLLK85 PKG.M0.6BL.LZ PLC.M1.0SL.LA GMA.10.290.DN GMA.3B.090.DA PRG.M0.6GL.LC52GZ PSA.1S.275.CTLC66 ABF.1S.250.NTA 133020F 1331ER193MZ 1332M107MZ DTS26Z19-32JA-LC DTS26Z19-32SA DTS26Z19-32SA-LC DTS26Z23-55HA DTS26Z23-55HA-LC DTS26Z23-55JA-LC EAJ.1B.306.CWA ECG.XB.312.CLL 1589430-2 EEA.0B.305.CLN EEA.0B.309.CLL ELF.00.250.NTL ERA.01.250.DLL BRR.2S.200.PZVG HR10A-P CAH.M34.SLL.C72GZ CAJ.M34.SLL.C72GZ 300500 ESB.00.303.NLL EXG.0B.309.HLN FFB.1S.250.CLAC27 FGA.2B.306.CYCD92 FGA.2B.306.CYCD92Z FGA.XB.312.CLAD72 FGJ.1B.302.CYMD62 FGJ.3B.308.CLLD72Z