

# HEG.1K.304.CLLPV

# **SUMMARY**

#### # Wires

Low voltage 4



Image is for illustrative purpose only

Series 1K

**Termination type** Female solder

IP rating 68

AWG wire size 30.00 - 22.00

Cable Ø 0.00 - 0.00 mm

Status active

Matching parts FGG.1K.304.CLAC20Z

### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### Mechanics

Shell Style/Model HE\*: Fixed receptacle, nut fixing, watertight or vacuum-tight (back panel mounting)

**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Variant PV: Watertight / Vacuum-tested

Weight 22.12 g

#### **Performance**

Configuration 1K.304: 4 Low Voltage
Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 10 Amps

### **Specifications**

Contact Type: Solder

Contact Dia.: 0.9 mm (0.035in) Bucket Dia.: 0.8 mm (0.031in)

Max. Solid Conductor: 0.34 mm<sup>2</sup> (AWG 22) Max. Stranded Conductor: 0.34 mm<sup>2</sup> (AWG 22)

R (max): 4.8 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 1450 V (AC), 2050 V (DC) Vtest (contact-contact): 1350 V (AC), 1910 V (DC)

### **Others**

Endurance (Shell): 5000 mating cycles Temp (min / max): -20°C / +100°C

Humidity (max): <=95% [at 60 deg C /140 F]


Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 20/80/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz)

R leak (He) (max): 0.0000001 mbar\*l/s (if vacuum-tested)

Salt Spray Corrosion: >1000 hr

Pressure: 60 bars

# **DRAWINGS**



#### **Dimensions**

	А	В	Е	L	М	Р	S1	e
mm.	20	20	6.2	30	3.5	10	14.5	M16x1.0
in.	0,79	0,79	0,24	1,18	0,14	0,39	0,57	

# **RECOMMENDED BY LEMO**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Tools**

### **Cables**

CMN.04.T22.047QGC	TPR	Grey	
CMN.04.T22.048QGZE	TPR (medical)	Grey	> -
CMN.04.T28.031PGCE	PVC	GREY	
CMN.04.T28.031PGZE		Grey	>
CMN.04.T28.031PNCE	PVC	Black	>=====================================
CMN.04.T28.031PNZE			>——€
CMN.04.T28.031QGC	TPR	Grey	
140240	PVC	Black	
140250	PVC	Grey	<b>&gt;</b>
40080	PVC	Black	
40086	PVC	Blue	
40140	PVC	Black	
40240	PTFE	White	<b>&gt;</b> <
40260	PVC	Black	
4041	PVC	Grey	> €
4050	PVC	Black	
4080	PVC	Grey	
417920	PVC	Grey	
4220	PVC	Black	
4221	PVC	Black	-
4260	PTFE	White	>====
4280	PVC	Black	
80080	PVC	Grey	
80082	PVC	Red	
80084	PVC	Black	
CTR.75.030.121870G	PVC	Grey	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# **X-ON Electronics**

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Circular Push Pull Connectors category:

Click to view products by LEMO manufacturer:

Other Similar products are found below:

6407-249V-11273P 6408-201V-13273 6408-202V-13343 6408-202V-17343 EZG.0B.309.CLN FFA.2S.310.ZLA FGA.1B.307.CYCD72Z FGJ.1B.304.CLLD76 FGJ.1B.306.CWLD72 FGJ.3B.304.CYMD10Z FGJ.3B.304.CYMD82Z PCS.01.250.DLLE24 PHG.0K.305.CYMC40Z PHG.1K.308.CLLK85 PKG.M0.6BL.LZ PLC.M1.0SL.LA GMA.10.290.DN GMA.3B.090.DA PRG.M0.6GL.LC52GZ PSA.1S.275.CTLC66 ABF.1S.250.NTA 133020F 1331ER193MZ 1332M107MZ DTS26Z19-32JA-LC DTS26Z19-32SA DTS26Z19-32SA-LC DTS26Z23-55HA DTS26Z23-55HA-LC DTS26Z23-55JA-LC EAJ.1B.306.CWA ECG.XB.312.CLL 1589430-2 EEA.0B.305.CLN EEA.0B.309.CLL ELF.00.250.NTL ERA.01.250.DLL BRR.2S.200.PZVG HR10A-P CAH.M34.SLL.C72GZ CAJ.M34.SLL.C72GZ 300500 ESB.00.303.NLL EXG.0B.309.HLN FFB.1S.250.CLAC27 FGA.2B.306.CYCD92 FGA.2B.306.CYCD92Z FGA.XB.312.CLAD72 FGJ.1B.302.CYMD62 FGJ.3B.308.CLLD72Z