Document Number: MPX2300DT1 Rev. 11, 09/2015

VRoHS

MPX2300DT1, 0 to 40 kPa, Differential Compensated Pressure Sensor

Freescale Semiconductor has developed a high volume, miniature pressure sensor package which is ideal as a sub-module component or a disposable unit. The unique concept of the Chip Pak allows great flexibility in system design while providing an economic solution for the designer. This new chip carrier package uses Freescale Semiconductor's unique sensor die with its piezoresistive technology, along with the added feature of on-chip, thin-film temperature compensation and calibration.

Features

- Integrated temperature compensation and calibration
- · Ratiometric to supply voltage
- Polysulfone case material (ISO 10993)
- Provided in easy-to-use tape and reel


Typical applications


- Medical diagnostics
- Infusion pumps
- · Blood pressure monitors
- Pressure catheter applications
- Patient monitoring

NOTE

The die and wire bonds are exposed on the front side of the chip pak (pressure is applied to the backside of the device). Front side die and wire protection must be provided in the customer's housing. Use caution when handling the devices during all processes.

MPX2300DT1





Ordering information						
Device name	Oli immirra		Pressure type			Davies medica
Device name	Shipping	Package Gauge Differential Absolute	Absolute	Device marking		
MPX2300DT1	Tape and Reel	98ASB13355C		•		XXXX = Device code XXX = Trace code

Freescale reserves the right to change the detail specifications as may be required to permit improvements in the design of its products.

© 2010, 2012, 2014, 2015 Freescale Semiconductor, Inc. All rights reserved.





Contents

1	General Description	3
	1.1 Block diagram	3
	1.2 Pinout	3
2	Mechanical and Electrical Specifications	4
	2.1 Maximum ratings	4
	2.2 Operating characteristics	4
	Package Dimensions	
	3.1 Package description	
4	Devision History	_

Related Documentation

The MPX2300DT1 device features and operations are described in a variety of reference manuals, user guides, and application notes. To find the most-current versions of these documents:

1. Go to the Freescale homepage at:

http://www.freescale.com/

- 2. In the Keyword search box at the top of the page, enter the device number MPX2300DT1.
- 3. In the Refine Your Result pane on the left, click on the Documentation link.

MPX2300DT1



1 General Description

The MPX2300DT1 pressure sensor has been designed for medical usage by combining the performance of Freescale's shear stress pressure sensor design and the use of biomedically approved materials. Materials with a proven history in medical situations have been chosen to provide a sensor that can be used with confidence in applications, such as invasive blood pressure monitoring. It can be sterilized using ethylene oxide. The portions of the pressure sensor that are required to be biomedically approved are the rigid housing and the gel coating.

The rigid housing is molded from a white, medical grade polysulfone that has passed extensive biological testing including: ISO 10993-5:1999, ISO 10993-10:2002, and ISO 10993-11:1993.

A silicone dielectric gel covers the silicon piezoresistive sensing element. The gel is a nontoxic, nonallergenic elastomer system which meets all USP XX Biological Testing Class V requirements. The properties of the gel allow it to transmit pressure uniformly to the diaphragm surface, while isolating the internal electrical connections from the corrosive effects of fluids, such as saline solution. The gel provides electrical isolation sufficient to withstand defibrillation testing, as specified in the proposed Association for the Advancement of Medical Instrumentation (AAMI) Standard for blood pressure transducers. A biomedically approved opaque filler in the gel prevents bright operating room lights from affecting the performance of the sensor.

1.1 Block diagram

Figure 1 shows a block diagram of the internal circuitry integrated on a pressure sensor chip.




Figure 1. Block diagram

1.2 Pinout




Figure 2. Device pinout (front view)

Table 1. Pin functions

Pin	Name	Function
1	V _S	Voltage supply
2	V _{OUT} +	Output voltage
3	V _{OUT} -	Output voltage
4	GND	Ground

MPX2300DT1



2 Mechanical and Electrical Specifications

2.1 Maximum ratings

Table 2. Maximum ratings⁽¹⁾

Rating	Symbol	Value	Unit
Maximum pressure (backside)	P _{max}	125	PSI
Storage temperature	T _{stg}	-25 to +85	°C
Operating temperature	T _A	+15 to +40	°C

^{1.} Exposure beyond the specified limits may cause permanent damage or degradation to the device.

2.2 Operating characteristics

Table 3. Operating characteristics ($V_S = 6 V_{DC}$, $T_A = 25 °C$ unless otherwise noted)

Characteristics	Symbol	Min	Тур	Max	Unit
Pressure range	P _{OP}	0	_	300	mmHg
Supply voltage ⁽¹⁾	V _S	_	6.0	10	V_{DC}
Supply current	Io	_	1.0	_	mAdc
Zero pressure offset	V _{OFF}	-0.75	_	0.75	mV
Sensitivity	_	4.95	5.0	5.05	μV/V/mmHg
Full-scale span ⁽²⁾	V _{FSS}	2.976	3.006	3.036	mV
Linearity + Hysteresis ⁽³⁾	_	-1.5	_	1.5	%V _{FSS}
Accuracy $V_S = 6 \text{ V}$, $P = 101 \text{ to } 200 \text{ mmHg}$	_	-1.5	_	1.5	%
Accuracy V _S = 6 V, P = 201 to 300 mmHg	_	-3.0	_	3.0	%
Temperature effect on sensitivity	TCS	-0.1	_	+0.1	%/°C
Temperature effect on full-scale span ⁽⁴⁾	TCV _{FSS}	-0.1	_	+0.1	%/°C
Temperature effect on offset ⁽⁵⁾	TCV _{OFF}	-9.0	_	+9.0	μV/°C
Input impedance	Z _{IN}	1800	_	4500	Ω
Output impedance	Z _{OUT}	270	_	330	Ω
$R_{CAL} (150 \text{ k}\Omega)^{(6)}$	R _{CAL}	97	100	103	mmHg
Response time ⁽⁷⁾ (10% to 90%)	t _R	_	1.0	_	ms

^{1.} Recommended voltage supply: 6 V ± 0.2 V, regulated. Sensor output is ratiometric to the voltage supply. Supply voltages above +10 V may induce additional error due to device self-heating.

Measured at 6.0 V_{DC} excitation for 100 mmHg pressure differential. V_{FSS} and FSS are like terms representing the algebraic difference between full scale output and zero pressure offset.

^{3.} Maximum deviation from end-point straight line fit at 0 and 200 mmHg.

^{4.} Slope of end-point straight line fit to full scale span at 15 °C and +40 °C relative to +25 °C.

^{5.} Slope of end-point straight line fit to zero pressure offset at 15 °C and +40 °C relative to +25 °C.

^{6.} Offset measurement with respect to the measured sensitivity when a 150 k resistor is connected to V_S and V_{OUT}+ output.


^{7.} For a 0 to 300 mmHg pressure step change.




Package Dimensions 3

3.1 Package description

This drawing is located at http://cache.freescale.com/files/shared/doc/package_info/98ASB13355C.pdf.





- NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.240	0.260	6.10	6.60	
В	0.350	0.370	8.89	9.40	
С	0.140	0.150	3.56	3.81	
D1	0.012	0.020	0.30	0.51	
D2	0.014	0.022	0.36	0.56	
Е	0.088	0.102	2.24	2.59	
F	0.123	0.128	3.12	3.25	
G	0.045	0.055	1.14	1.40	
Н	0.037	0.047	0.94	1.19	
J	0.007	0.011	0.18	0.28	
K	0.120	0.140	3.05	3.56	
L	0.095	0.105	2.41	2.67	
M	0.165	0.175	4.19	4.45	
N	0.223	0.239	5.66	6.07	
٧	0.105	0.115	2.67	2.92	
AA	0.095	0.107	2.41	2.72	
AB	0.015	0.035	0.38	0.89	
AC	0.120	0.175	3.05	4.45	
AD	0.100	0.115	2.54	2.92	

Case 98ASB1335C, Chip Pak package



4 Revision History

Table 4. Revision history

Revision number	Revision date	Description	
9	10/2012	Added Table 1. Pin Numbers on page 1.	
10	09/2015	Updated format.	
11	09/2015	 Corrected pinout on first page and Section 1.2 and Table 1. Replaced Figure 1, Block diagram. 	



How to Reach Us:

Home Page: freescale.com

Web Support:

freescale.com/support

Information in this document is provided solely to enable system and software implementers to use Freescale products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document.

Freescale reserves the right to make changes without further notice to any products herein. Freescale makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. Freescale does not convey any license under its patent rights nor the rights of others. Freescale sells products pursuant to standard terms and conditions of sale, which can be found at the following address: freescale.com/salestermsandconditions.

Freescale and the Freescale logos are trademarks of Freescale Semiconductor, Inc., Reg. U.S. Pat. & Tm. Off. All other product or service names are the property of their respective owners.

© 2010, 2012, 2014, 2015 Freescale Semiconductor, Inc.

Document Number: MPX2300DT1

Rev. 11 09/2015



X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Board Mount Pressure Sensors category:

Click to view products by NXP manufacturer:

Other Similar products are found below:

6407-249V-17343P 6407-250V-09273P 80527-25.0H2-05 80541-B00000150-01 80541-B00000200-05 80554-00700100-05 8056800300050-01 93.631.4253.0 93.731.4353.0 93.932.4553.0 136PC150G2 136PC15A1 142PC95AW71 142PC05DW70 15PSI-G-4V 180501A-L0N-B 26PCBKT 26PCCFA6D26 26PCCFS2G 26PCCVA6D 93.632.7353.0 93.731.3653.0 93.931.4853.0 93.932.4853.0 SCDA120XSC05DC 185PC30DH 20INCH-G-MV-MINI 26PCAFJ3G 26PCCEP5G24 26PCDFA3G 26PCJEU5G19 ASCX15AN-90
TSCSAAN001PDUCV DCAL401DN DCAL401GN XZ202798SSC XZ203676HSC 6407-249V-09343P 6407-250V-17343P SP370-25-1160 81794-B00001200-01 HSCDLNN100PGAA5 82681-B00000100-01 81618-B00000040-05 SSCDJNN015PAAA5 TSCDLNN100MDUCV
TSCSAAN100PDUCV NBPDANN015PGUNV NBPLLNS150PGUNV 142PC100D