

Kelvin-Entwicklungsset

bestehend aus:

- 4 Kelvin-Buchsen:
2 x **KBU 7992 L Au / SW**,
2 x **KBU 7992 L Au / RT**
- 4 Kelvin-Messleitungen:
2 x **KML 7848 Au / PZ / 150 / SW**,
2 x **KML 7848 Au / PZ / 150 / RT**
- 4 Kelvin-Messleitungen:
2 x **KML 7852 Au / SAK / 150 / SW**,
2 x **KML 7852 Au / SAK / 150 / RT**

Weitere technische Daten
finden sich in den einzelnen
Produktdatenblättern.

Best.-Nr. SET 8606 / KELVIN-ENTWICKLUNG**Kelvin measuring set**

consisting of:

- 4 kelvin sockets:
2 x **KBU 7992 L Au / SW**,
2 x **KBU 7992 L Au / RT**
- 4 kelvin measuring leads:
2 x **KML 7848 Au / PZ / 150 / SW**,
2 x **KML 7848 Au / PZ / 150 / RT**
- 4 kelvin measuring leads:
2 x **KML 7852 Au / SAK / 150 / SW**,
2 x **KML 7852 Au / SAK / 150 / RT**

Please see product data sheets
for further technical details.

Order No. SET 8606 / KELVIN-ENTWICKLUNG**Allgemeine Angaben****Best.-Nr.** SET 8606 / KELVIN-ENTWICKLUNG**Technische Daten****General information****Order No.** SET 8606 / KELVIN-ENTWICKLUNG**Technical data**

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [Test Leads](#) category:

Click to view products by [SCHUTZINGER](#) manufacturer:

Other Similar products are found below :

[R928010000](#) [R928142000](#) [1301430020](#) [15101](#) [15115](#) [15117](#) [15301](#) [15303](#) [15304](#) [15102](#) [15120](#) [15308](#) [15408](#) [15302](#) [15306](#) [15307](#) [15502](#)
[15403](#) [15407](#) [15409](#) [15501](#) [15506](#) [EM3782-12-7#](#) [EM4702-12-0](#) [BU-1149-A-36-0](#) [BU-1481-E-12-0](#) [BU-1481-E-24-0](#) [2524-A-60](#) [924961-C](#)
[924964-C](#) [924966-C](#) [924967-C](#) [LB1F-2R-RED](#) [LB1F-2R-YLW](#) [2500](#) [2501](#) [2524-A-48](#) [2977-J-48](#) [R928051000](#) [R928141000](#) [R928143000](#)
[R948131000](#) [BU-1449-E-12-2](#) [BU-1480-E-24-0](#) [BU-1481-E-12-2](#) [BU-1481-E-24-2](#) [LB1F-2R-BLK](#) [LB1F-2R-BLUE](#) [EM3542-1#](#) [EM3782-12-8#](#)