



Zero Charge Hand Lotion Product# 1702

Product Description

Improves contact between personnel and grounding devices such as wrist straps and heel straps. Does not contain silicone, lanolin, mineral oil and other materials found in conventional hand lotions that can interfere with PCB manufacturing. Blend of moisturizers, aloe vera, and vitamins A and E penetrate rapidly leaving skin soft without a greasy film.

Features / Benefits

- Improves wrist and heel strap contact
- Does not contain silicone or lanolin
- Non-contaminating / does not interfere with soldering
- Non-greasy
- Nonflammable

Solderability Inhibitors

Hand lotions from other manufacturers can contain ingredients that will contaminate the work surface and inhibit solderability. Zero Charge Hand Lotion does not contain any of these ingredients.

Ingredient	
Glycerin	NO
Grease	NO
Lanolin	NO
Mineral Oils	NO
Silicone	NO

Usage Instructions

Apply small amount of lotion to hands and wrists. Massage into skin. Use at start of day, after hands have been washed or anytime skin is dry.



Typical Product Data and Physical Properties

Physical state:	Liquid
Color:	White
Odor:	Pleasant
pH:	7.2
Boiling/condensation point:	212°F (100°C)
Melting/freezing point:	32°F (0°C)
Relative density:	1
Shelf life:	5 years

Zero Charge Hand Lotion Product# 1702

Packaging and Availability

1702-8FP	8 oz liquid
1702-G	1 gallon liquid

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [Chemicals](#) category:

Click to view products by [Techspray](#) manufacturer:

Other Similar products are found below :

[DP-605NS](#) [3045-QT](#) [3125-9S](#) [5200-WHITE-3OZ](#) [3748-Q-58"x8"](#) [FO-25DT](#) [S1009-KIT-A-CS8606](#) [DP100-200ML](#) [1743-2FP](#) [152-KA-NC](#)
[826-450G](#) [9729](#) [9223](#) [9945](#) [7000000275](#) [1601](#) [8330-19G](#) [842AR-15ML](#) [841AR-150ML](#) [842AR-P](#) [843WB-15ML](#) [8462-85ML](#) [4354-1L](#)
[838AR-P](#) [838AR-15ML](#) [419D-P-BK](#) [419D-P-GR](#) [419D-P-WH](#) [8MT-450](#) [8MT-25](#) [832HD-25ML](#) [8616-25ML](#) [832FX-450ML](#) [834ATH-](#)
[375ML](#) [832HD-400ML](#) [8617-1P](#) [843AR-340G](#) [9310-300ML](#) [847-1P](#) [4228-225ML](#) [419D-55ML](#) [8800-375ML](#) [8810-375ML](#) [8820-2.55L](#)
[419E-340G](#) [842UR-12ML](#) [419D-1L](#) [CW3300WHITE](#) [CW2205](#) [10447](#)