

### **Electronics**

## **MicroFit**

# Raychem

# Small diameter, high shrink ratio, heat-shrinkable tubing

MicroFit tubing is micro-sized, heatshrinkable tubing that offers a high shrink ratio (up to 3:1) and fits a range of diameters from .007" to .045". It is offered in a variety of materials including two medical-grade formulations from our Altera line of medicalgrade, heat-shrinkable tubing products.

MicroFit tubing provides electrical insulation, mechanical protection, and strain relief in the smaller, more compact medical devices and commercial electronics products manufactured today. MicroFit tubing's high shrink ratio eases installation since the tubing's diameter is large enough to slide easily over the micro-sized substrate.

Yet, upon heating, the same tubing shrinks to fit tightly on a wide range of substrate diameters.

MicroFit tubing is offered in three materials: RW-175, MT1000, and MT2000. MT1000 and MT2000 meet the requirements of U.S. Pharmacopeia (USP) Class VI.

RW-175 and MT1000 tubings utilize a tough semirigid fluoropolymer. They are especially suitable for applications requiring hightemperature performance, outstanding resistance to abrasion and cut-through, and excellent resistance to a variety of fluids. RW-175 meets NASA requirements for low-outgassing materials. MTI000 tubing may be sterilized by radiation, ethylene oxide, steam, and dry heat with no significant change in physical properties.

MT2000 tubing is made from a tough, modified polyolefin that offers flexibility, lubricity, and good electrical insulation performance. MT2000's low shrink temperature enables the tubing to shrink faster than other materials with similar attributes, thereby reducing the risk of damage to temperature-sensitive substrates. MT2000 tubing may be sterilized by gamma radiation or ethylene oxide with no significant change in physical properties.

Temperature rating		
RW-175, MT1000		
Full recovery temperature:	175°C	
Continuous operating temperature:	−55°C to 175°C	
Recommended maximum temperature for use as a primary insulator:	135°C	
MT2000		
Full recovery temperature:	140°C	
Continuous operating temperature:	-40°C to 105°C	

Specifications*			
Туре	Raychem	Material	Master File Number
RW-175	RW-175 MicroFit SCD		
MT1000, MT2000	Altera MicroFit SCD	USP Class VI	MAF-444 (MT1000), MAF-727 (MT2000)
*When ordering always specify latest	iccup		

## Dimensions (millimeters/inches)



Inside diameter			Wall thickness		
	D (min.)	d (max.)	W1	W2 (max.)	
	Expanded	Recovered after	As supplied	Recovered	
Part number	as supplied	heating	(nominal)	after heating****	
MFT-**-No. 1-***	0.356 0.014	0.178 <i>0.007</i>	0.076 <i>0.003</i>	0.127 <i>0.005</i>	
MFT-**-No. 2-***	0.610 <i>0.024</i>	0.305 0.012	0.064 <i>0.0025</i>	0.152 <i>0.006</i>	
MFT-**-No. 33-***	1.143 <i>0.045</i>	0.432 <i>0.017</i>	0.064 <i>0.0025</i>	0.118 <i>0.007</i>	
MFT-**-No. 65-***	0.635 <i>0.025</i>	0.254 <i>0.010</i>	0.127 <i>0.005</i>	0.330 <i>0.013</i>	

<sup>\*\*</sup>Replace double asterisk with material number: RW-175, MT1000 or MT2000 \*\*\*Replace triple asterisk with color-code number: \*\*\*\*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Colors		RW-175, MT1000	MT2000	
	Standard	Clear	Black, clear	
	Nonstandard	Black	White, red, yellow, blue, orange	
Size selection	Always order the largest size that will shrink snugly over the component being covered.			
A variety of special order sizes may be made available upon request.				
Standard packaging	In 4-foot lengths (RW-175); on plastic spools, double-bagged (MT1000, MT2000)			
Ordering description	Specify product name, material type, size, and color; for example, MFT-MT2000-No.1-0 (0=Black).			

#### RW-175 MicroFit specification values

	Property	Unit	Requirement	Method of test
Physical	Dimensions	mm (inches)	See reverse	ASTM D 2671
	Tensile strength	psi <i>(MPa)</i>	5000 <i>(34.5)</i> minimum	ASTM D 2671
				2" per minute
	Ultimate elongation	percent	150 minimum	ASTM D 2671
				2" per minute
	Secant modulus (expanded)	psi <i>(MPa)</i>	1 x 10 <sup>5</sup> <i>(690)</i> minimum	ASTM D 2671
	Heat shock		No dripping, flowing	AMS-DTL-23053,
	(4 hours at 300°C/572°F)		or cracking	5/16" mandrel
	Low temperature flexibility		No cracking after wrapping	ASTM D 2671
	(4 hours at -55°C/-67°F)		on mandrel	Procedure C
				5/16" mandrel
Electrical	Dielectric strength	volts/mil (volts/mm)	800 <i>(31,500)</i> minimum	ASTM D 2671

#### Altera MicroFit specification values

	Property	Unit	Requirement	Method of test
Physical	Dimensions	mm (inches)	See reverse	ASTM D 2671
	Tensile strength	psi <i>(MPa)</i>		ASTM D 2671
	MT1000 MT2000		5000 <i>(34.5)</i> minimum 3000 <i>(20.7)</i> minimum	2" per minute
	Ultimate elongation	percent		ASTM D 2671
	MT1000 MT2000	·	150 minimum 200 minimum	2" per minute
	Secant modulus (expanded) MT1000 MT2000	psi <i>(MPa)</i>	1.0 X 10 <sup>5</sup> <i>(690)</i> minimum 5.0 X 10 <sup>4</sup> <i>(344)</i> minimum	ASTM D 2671
Electrical	Dielectric strength MT1000 MT2000	volts/mil (volts/mm)	800 <i>(31,500)</i> minimum 1000 <i>(39,360)</i> minimum	ASTM D 2671
	Dielectric withstand 3000 V, 60 Hz	seconds	60 minimum	ASTM D 2671
Chemical	Heavy metals analysis Cadmium Mercury Lead Bismuth Antimony	ppm	1 maximum (total of all metals)	USP XXII Physiochemical Tests - Plastics (See note below)

Note: Sample preparation and extraction is per USP XXII. Metals analysis may be colorimetric as described in USP XXII or by equivalent quantitive analytical method.

Altera, Raychem, and MicroFit are trademarks of Tyco Electronics Corporation.

#### Users should independently evaluate the suitability of the product for their application.

Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA 94025-1164 USA Tel: (800) 926-2425 (US & Canada) Tel: +1 (650) 361-3860 (All other countries)

Faraday Road Dorcan, Swindon, SN3 5HH United Kingdom Tel: +44 1793 528171 3816 Noborito, Tama-ku Kawasaki, Kanagawa 214-8533 Japan Tel: +81 44 900 5102 Asia Pacific Headquarters 26 Ang Mo Kio, Industrial Park 2 Singapore 569507 Tel: +65 4866 151

All information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics Corporation makes no warranties as to the accuracy or completeness of the information, and disclaims any liability regarding its use. Tyco Electronics Corporation's only obligations are those in the Standard Terms and Conditions of Sale for these products and in no case will Tyco Electronics Corporation be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of the product. Tyco Electronics Corporation's Specifications are subject to change without notice. In addition, Tyco Electronics Corporation reserves the right to make changes in materials or processing without notification to the Buyer which do not affect compliance with any applicable specification.

# **X-ON Electronics**

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Heat Shrink Tubing and Sleeves category:

Click to view products by TE Connectivity manufacturer:

Other Similar products are found below:

770-006S102 5685710001 CR8248-000 CR9960-000 603312-4 607381P039 611112-000 617867N001 6500750004 CZ1420-000 D-306-38 770-003S106W2 770-005S105W1 770-005S106W1 770-007A303 770-010Y106W1 770-010Y706W1 7771210001 MFP-1/4"-Clear MFP-3/64"-Clear 790-3012 MFT-MT2000-NO.14-0-SP MHHT-4-15K2-G-104 MIL-LT-1-1/2-4-SP MIL-LT-1-1/2-9-STK MIL-LT-1/2-2-STK MIL-LT-3-0-SP MIL-LT-3/32-0-SP MIL-LT-3/32-6-SP MIL-LT-3/4-6-SP MIL-LT-3/8-0-SP 8159270001 839602-000 8423-6 FP301-116-6"-Black FP301-1/2-48"-Black FP301-12-48"-Black-Hdr FP301-1/4-48"-Black FP301-1/4-48"-White-Hdr FP301-18-48"-Black-Hdr FP301-1/8-6"-Black FP301-18-6"-Black FP301-316-48"-Blue-Hdr FP301-316-6"-Clear FP301-332-6"-Black 912229N002 120-126-16BL 121-001-09 121-018-32 121-018-40