
## Altera<sup>™</sup> MT2000 Modified, Medical Grade, Polyolefin, Heat - Shrinkable Tubing



This specification covers the requirements for one type of single wall, electrical insulating, extruded tubing whose diameter will reduce to a predetermined size upon application of heat in excess of 140°C (284°F).

The tubing is fabricated from modified polyolefin crosslinked by irradiation. It shall be homogenous and essentially free from flaws, defects, pinholes, seams, cracks or inclusions.

The tubing is fabricated from materials which meet the requirements of U.S. Pharmacopeia Class VI Plastics. Color shall be black or clear unless otherwise specified.

**Table 1: Dimensions** 

	As Supplied			Recovered							
				Inside Diameter Wall Thickness(Inches Maximum (d) (W)				, Millimeters)			
	mm.	in.	mm.	in.	Minimum		Maximum		Nominal		
1mm	1.0	.040	0.45	.018	.008	0.20	.012	0.30	.010	.25	
2mm	2.0	.080	0.80	.032	.008	0.20	.012	0.30	.010	.25	
3mm	3.0	.120	1.20	.048	.008	0.20	.012	0.30	.010	.25	
6mm	6.0	.240	2.4	.096	.008	0.20	.012	0.30	.010	.25	
10mm	10.0	.400	4.0	.160	.012	0.30	.016	0.41	.014	.36	

TE Connectivity

TE Constitutional Drive

Raychem

Title: Altera™MT2000

	300 Constitutional Dri Menlo Park, CA 9402		nayonom	Modified, Medical Grade, Polyolefin, Heat - Shrinkable Tubing		
	rves the right to amend to evaluate the suitability of		Document No :	MT2000		
Cage Code: 06090	Scale: None	Size: A	Rev. Date: 11MAY11	Rev.: B1	Sheet: 1 of 2	

Print Date: 11-May-11 If this document is printed it becomes uncontrolled. Check for the latest revision.

Table 2: Properties

Property	Unit	Requirement	Test Method	
PHYSICAL				
* Dimensions	Inches (mm)	In accordance with Table 1		
* Longitudinal Change	Percent	0, -10	ASTM D 2671	
* Concentricity as supplied	Percent	60 minimum	ASTM D 2671	
Tensile Strength	PSI (MPa)	3000 minimum (20.7)	ASTM D 2671,	
Ultimate Elongation	Percent	200 minimum	2"/minute	
Secant Modulus	PSI (MPa)	5.0 x 10 <sup>4</sup> minimum <i>(344)</i>	ASTM D 2671	
Heat Resistance				
168 hours at 125℃ (257 ℉)				
Followed by test for:			ASTM D 2671,	
Ultimate Elongation	Percent	200 minimum	2"/minute	
ELECTRICAL				
Dielectric Strength	Volts/mil	1000 minimum (39.36)	ASTM D 2671	
	(volts/mm)			
Dielectric Withstand				
3000V, 60 Hz	sec	60 minimum	ASTM D 2671	
CHEMICAL				
Fluid Resistance			ASTM D 2671	
24 hours at 23 ± 3℃ (77 ± 5年)				
Isopropyl Alcohol				
5% Saline Solution				
Cidex**				
Followed by tests for:				
Dielectric Strength	Volts/mil	1000 minimum (39.36)	ASTM D 2671	
	(volts/mm)			
Tensile Strength	PSI (MPa)	3000 minimum <i>(20.7)</i>	ASTM D 2671	
Heavy Metals Analysis	ppm	1 maximum	USP XXII	
Cadmium		(total of all metals)	Physicochemical	
Mercury			Tests-Plastics	
Lead			(Note 1)	
Bismuth				
Antimony				

<sup>\*</sup> Denotes lot acceptance test

Note 1: Sample preparation and extraction is per USP XXII. Metals analysis may be colorimetric as described in USP XXII or by equivalent quantitative analytical method.

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

Rev. Date:	Rev.:	Document No.	Sheet:
11MAY11	B1	MT2000	2 of 2

<sup>\*\*</sup>Trademark of Johnson & Johnson Company

## **X-ON Electronics**

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Heat Shrink Tubing and Sleeves category:

Click to view products by TE Connectivity manufacturer:

Other Similar products are found below:

770-006S102 5685710001 CR8248-000 CR9960-000 603312-4 607381P039 617867N001 6500750004 D-306-38 770-003S106W2 770005S105W1 770-005S106W1 770-007A303 770-010Y106W1 770-010Y706W1 7771210001 MFP-1/4"-Clear MFP-3/64"-Clear 790-3012
MFT-MT2000-NO.14-0-SP MHHT-4-15K2-G-104 MIL-LT-1-1/2-4-SP MIL-LT-1-1/2-9-STK MIL-LT-1/2-2-STK MIL-LT-3/0-SP MIL-LT3/32-0-SP MIL-LT-3/32-6-SP MIL-LT-3/4-6-SP MIL-LT-3/8-0-SP 8159270001 839602-000 8423-6 FP301-116-6"-Black FP301-1/2-48"Black FP301-12-48"-Black-Hdr FP301-1/4-48"-Black FP301-1/4-48"-White-Hdr FP301-18-48"-Black-Hdr FP301-1/8-6"-Black FP301-186"-Black-Bulk FP301-316-48"-Blue-Hdr FP301-316-6"-Clear FP301-332-6"-Black 912229N002 120-126-16BL 121-001-09 121-018-32
121-018-40 121-123-1-1-32BTC 121-123-1-1-40BTC