CYAN MAGENTA YELLOW BLACK CYAN MAGENTA YELLOW BLACK

TGP110 10MHz pulse generator with delay

An essential instrument

The generation of pulses for the stimulus and control of electronic systems is beyond the capability of all but the most sophisticated of function generators.

The architecture of a dedicated pulse generator enables it to generate pulses of a set width regardless of the repetition rate offering duty cycles which can extend down to 1 in 100 million.

In addition to continuous operation, single or multiple pulses can be generated in response to trigger or gating signals with precisely defined timing relationships.

A dedicated pulse-waveform output amplifier provides flat top pulses with fast rise and fall times at variable amplitude.

Variable delay

The TGP110 offers selectable delay between the sync output and pulse output. In triggered mode this also sets the delay between a trigger signal and the start of the pulse.

PERIOD, PULSE WIDTH, DELAY

Each parameter is variable within 8 overlapping decade ranges with a vernier providing continuously variable control within each range.

PERIOD 100nsec to 10sec (10MHz to 0·1Hz). Range:

PULSE WIDTH

Range: 50nsec to 5sec <0.1%.

DFI AY

50nsec to 5sec Range:

TRIGGER, GATE

Normal operational mode in which pulses are generated continuously at 0.1Hz to 10MHz.

TRIGGERED

DC to 10MHz pulse train in synchronism with external trigger pulses; pulse width determined by pulse width controls. Trigger can be generated manually from front panel button.

GATED

0.1Hz to 10MHz pulse train, parameters set by period and pulse width controls, starts synchronously with leading edge of gate input. Last pulse is completed at the end of gating period. Gating signal can be generated manually from front panel button

PULSE MODES

NORMAL PULSE

One pulse is generated each period. The delay setting is ignored. **SQUAREWAVE**

0.1Hz to 10MHz squarewave, frequency set by the period controls. Pulse width and delay settings ignored.

Mark: Space ratio: 1:1 ±10%.

DOUBLE PULSE

A second pulse is generated after a delay set by the delay controls; the delay is related to the leading edge of the first pulse.

DELAYED PULSE

A pulse is generated after a delay set by the delay controls; the delay is related to rising edge of the trigger signal

Designed and built in Europe by:



Glebe Road, Huntingdon. Cambs. PE29 7DR England Tel: +44 (0)1480 412451 Fax: +44 (0) 1480 450409 Email: info@aimtti.com Web: www.aimtti.com

Wide pulse range

The TGP110 can generate pulse widths in the range 50ns to 5s. There are eight overlapping decade ranges with vernier control within each range.

The period range is 100ns to 10s, equivalent to a repetition rate range of 10MHz to 0.1Hz. Delay is independently adjustable over the same range as pulse width.

A complement switch inverts the mark-space polarity.

Squarewave and double pulse

In square mode, squarewaves are generated at a frequency set by the period controls alone. This provides a convenient means of generating variable period edges where the pulse width is unimportant, for example.

In double pulse mode, a second pulse is generated within every period at a set delay after the start of the first pulse. The delay is independently adjustable.

INPUTS

GATE/TRIG INPUT

DC - 10MHz Frequency range:

TTL threshold; max. input ±10V. Signal range:

Min. pulse width: Input Impedance: Typically $10k\Omega$.

OUTPUTS

50Ω OUTPUT

Amplitude:

Two switch selectable ranges of 0.1V - 1.0V and 1V - 10V from 50Ω . (50mV to 500mV and 500mV to 5V into 50Ω). Adjustable within ranges by a single

Rise/Fall Times: Typically 10nsec into 50Ω load. Maximum 15ns. Typically <5% for output set at >20% of range maxi-Aberrations:

mum, into 50Ω .

AUX OUTPUT

Duplicates 50Ω output but at a fixed CMOS/TTL level.

SYNC OUTPUT

Amplitude:

A positive going pulse at CMOS/TTL level. Timing: Leading edge starts >20nsec before the TTL/50 Ω output transition

Duration: Typically 30nsec.

COMPLEMENT SWITCH

Inverts the AUX and 50Ω outputs

GENERAL

230V or 115V AC nominal 50/60Hz, adjustable inter-Power: nally; operating range ±14% of nominal; 20VA max.

140 x 220 x 230mm (HxWxD) Size:

Weight: 1.6kg (3.5lb)

Operating Range: + 5°C to 40°C, 20-80% RH. Storage Range: - 40° C to 70° C

Complies with EN61010-1. Safety

EMC: Complies with EN55081-1 and EN50082-1.

Thurlby Thandar Instruments Ltd. operates a policy of continuous development and reserves the right to alter specifications without prior notice.





AIM & THURLBY THANDAR INSTRUMENTS **TGP110**



10MHz pulse generator with delay

- 0.1Hz to 10MHz frequency range
- 50ns minimum pulse width; fully variable pulse delay
- Squarewave, double pulse and delayed pulse modes
- Free-run, gated and triggered modes
- 50 Ω output, variable 0.1V to 10V; TTL and sync outputs



CYAN MAGENTA YELLOW BLACK CYAN MAGENTA YELLOW BLACK

TGP110 10MHz pulse generator with delay

An essential instrument

The generation of pulses for the stimulus and control of electronic systems is beyond the capability of all but the most sophisticated of function generators.

The architecture of a dedicated pulse generator enables it to generate pulses of a set width regardless of the repetition rate offering duty cycles which can extend down to 1 in 100 million.

In addition to continuous operation, single or multiple pulses can be generated in response to trigger or gating signals with precisely defined timing relationships.

A dedicated pulse-waveform output amplifier provides flat top pulses with fast rise and fall times at variable amplitude.

Variable delay

The TGP110 offers selectable delay between the sync output and pulse output. In triggered mode this also sets the delay between a trigger signal and the start of the pulse.

PERIOD, PULSE WIDTH, DELAY

Each parameter is variable within 8 overlapping decade ranges with a vernier providing continuously variable control within each range.

PERIOD 100nsec to 10sec (10MHz to 0·1Hz). Range:

PULSE WIDTH

Range: 50nsec to 5sec <0.1%.

DFI AY

50nsec to 5sec Range:

TRIGGER, GATE

Normal operational mode in which pulses are generated continuously at 0.1Hz to 10MHz.

TRIGGERED

DC to 10MHz pulse train in synchronism with external trigger pulses; pulse width determined by pulse width controls. Trigger can be generated manually from front panel button.

GATED

0.1Hz to 10MHz pulse train, parameters set by period and pulse width controls, starts synchronously with leading edge of gate input. Last pulse is completed at the end of gating period. Gating signal can be generated manually from front panel button

PULSE MODES

NORMAL PULSE

One pulse is generated each period. The delay setting is ignored. **SQUAREWAVE**

0.1Hz to 10MHz squarewave, frequency set by the period controls. Pulse width and delay settings ignored.

Mark: Space ratio: 1:1 ±10%.

DOUBLE PULSE

A second pulse is generated after a delay set by the delay controls; the delay is related to the leading edge of the first pulse.

DELAYED PULSE

A pulse is generated after a delay set by the delay controls; the delay is related to rising edge of the trigger signal

Designed and built in Europe by:



Glebe Road, Huntingdon. Cambs. PE29 7DR England Tel: +44 (0)1480 412451 Fax: +44 (0) 1480 450409 Email: info@aimtti.com Web: www.aimtti.com

Wide pulse range

The TGP110 can generate pulse widths in the range 50ns to 5s. There are eight overlapping decade ranges with vernier control within each range.

The period range is 100ns to 10s, equivalent to a repetition rate range of 10MHz to 0.1Hz. Delay is independently adjustable over the same range as pulse width.

A complement switch inverts the mark-space polarity.

Squarewave and double pulse

In square mode, squarewaves are generated at a frequency set by the period controls alone. This provides a convenient means of generating variable period edges where the pulse width is unimportant, for example.

In double pulse mode, a second pulse is generated within every period at a set delay after the start of the first pulse. The delay is independently adjustable.

INPUTS

GATE/TRIG INPUT

DC - 10MHz Frequency range:

TTL threshold; max. input ±10V. Signal range:

Min. pulse width: Input Impedance: Typically $10k\Omega$.

OUTPUTS

50Ω OUTPUT

Amplitude:

Two switch selectable ranges of 0.1V - 1.0V and 1V - 10V from 50Ω . (50mV to 500mV and 500mV to 5V into 50Ω). Adjustable within ranges by a single

Rise/Fall Times: Typically 10nsec into 50Ω load. Maximum 15ns. Typically <5% for output set at >20% of range maxi-Aberrations:

mum, into 50Ω .

AUX OUTPUT

Duplicates 50Ω output but at a fixed CMOS/TTL level.

SYNC OUTPUT

Amplitude:

A positive going pulse at CMOS/TTL level. Timing: Leading edge starts >20nsec before the TTL/50 Ω output transition

Duration: Typically 30nsec.

COMPLEMENT SWITCH

Inverts the AUX and 50Ω outputs

GENERAL

230V or 115V AC nominal 50/60Hz, adjustable inter-Power: nally; operating range ±14% of nominal; 20VA max.

140 x 220 x 230mm (HxWxD) Size:

Weight: 1.6kg (3.5lb)

Operating Range: + 5°C to 40°C, 20-80% RH. Storage Range: - 40° C to 70° C

Complies with EN61010-1. Safety

EMC: Complies with EN55081-1 and EN50082-1.

Thurlby Thandar Instruments Ltd. operates a policy of continuous development and reserves the right to alter specifications without prior notice.





AIM & THURLBY THANDAR INSTRUMENTS **TGP110**



10MHz pulse generator with delay

- 0.1Hz to 10MHz frequency range
- 50ns minimum pulse width; fully variable pulse delay
- Squarewave, double pulse and delayed pulse modes
- Free-run, gated and triggered modes
- 50 Ω output, variable 0.1V to 10V; TTL and sync outputs









Product Summary

Laboratory Power Supplies

Bench and system power supplies from 30 watts up to 1200 watts using linear, mixed-mode and PowerFlex regulation technologies.



Waveform Generators

Analog and digital (DDS) function generators, true arbitrary generators, arbitrary/function generators and pulse generators.

Precision Measurement Instruments

Benchtop DMMs, frequency counters, component measurement instruments (LCR), electronic dc loads, current probes.



RF and EMC Test Equipment

Spectrum analyzers, signal generators, frequency counters, power meters, emc measurement instruments.



Company name and product brands

Thurlby Thandar Instruments Ltd. (TTi) is one of Europe's leading manufacturers of test and measurement instruments.

Products have been sold under two brand names:





In the future, however, the full product range will be branded Aim-TTi.



This changeover will be gradual and many products will continue to carry the TTi or Aim brands for some time to come.

Web Addresses (URLs)

The preferred URL for obtaining information concerning Aim-TTi products

www.aimtti.com (international customers)

Customers in the UK should use the URL:

www.aimtti.co.uk

Customers in the USA should use the URL: www.aimtti.us

Note that previous URLs such as www.tti-test.com will continue to operate for the time being.

Designed and built in Europe by:



Thurlby Thandar Instruments Ltd.

Glebe Road, Huntingdon, Cambridgeshire PE29 7DR England (United Kingdom)

Tel: +44 (0)1480 412451 Fax: +44 (0)1480 450409

Email: info@aimtti.com Web: www.aimtti.com

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for Inrush Current Limiters category:

Click to view products by TTI Aim manufacturer:

Other Similar products are found below:

B57234S330M SL12-22101-AT B57213P0800M301 MT8950AC SL22 20005-B B57235S0259M000V9 B57213P0470M351
B57213P0220M301 B57213P0109M301 B57211P0121M351 AS35 1R040 B57213P0709M301 B57211P0470M301 B57213P0330M301
B57213P0330M351 041337D CL-120AB SL22 2R515-A B57235S479MV9 B57237S0479M051V9 B57236S0259M051V9 SL03 50001
SL03 20001 NT03 10052 SL15 22101 SL08 4R003 SL15 5R007-A SL08 10001 SL22 16005 AS35 2R035 SL15 60004-A SL125R005
SL08 12101-A SL08 10002-A SL05-5R003 MS32 1R036-B MS32 15012-B MS22 12103-B MM35 1R550-DIN MM35 1R050 MM35
0R560-DIN MM35 0R280-DIN B57236S0229M000V9 CL-130A 33510B CL-80AB CL-140AB AS32 0R530-100 AS32 10015 AS32
1R030-100